


THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION


© COPYRIGHT - BY TYCO ELECTRONICS CORPORATION. ALL INTERNATIONAL RIGHTS RESERVED.

LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
G	14		J2	REV PER ECR 09—017201	30JUL09	JR	TM

AMP WIRE RANGE	 E13288 Listed	 LR7189 Certified
1/0 AWG SOLID OR STRANDED	1/0 AWG SOLID OR STRANDED	1/0 AWG SOLID OR STRANDED



25	SMALL		COPPER ASTM B-152 1.78 ±0.08 [.070 ±.003] ANNEALED	8-36916-3
50	STANDARD			36916
QTY	PACKAGE TYPE	FINISH	MATERIAL	PART NO.

MAX RECOMMENDED OPERATING TEMPERATURE: 170°C MAX	THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN DK SCHRUM 7/2/91		 Tyco Electronics Corporation Harrisburg, PA 17105-3608												
	DIMENSIONS: MM [INCHES]		CHK RD HEIM 8/15/91														
VOLTAGE RATING: N/A			TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD AJ KAUFMAN 8/16/91				NAME TERMINAL, RING TONGUE, SOLISTRAND, WIRE SIZE: 50.0mm2 [1/0] AWG								
			0 PLC ± - 1 PLC ± - 2 PLC ± 0.20[.008] 3 PLC ± - 4 PLC ± - ANGLES ± -		PRODUCT SPEC -												
CIRCULAR MIL AREA: 42.4-60.6mm² [83,700-119,500] SOLID OR STRANDED	MATERIAL SEE TABLE		FINISH SEE TABLE		APPLICATION SPEC -		SIZE		CAGE CODE		DRAWING NO		RESTRICTED TO				
					WEIGHT -		A3		00779		C-36916		-				
					CUSTOMER DRAWING						SCALE		2:1		SHEET		1 OF 1