


WIRELESS RECEPTACLE

R-075-J-DE



PROBE SPECIFICATIONS

Minimum Centers: .075 (1.91)

Drill Size: 1.45mm

Mounting Hole Size:
.055/.057 (1.40/1.45)

Spring Force: 2.7 oz. (77g) @
.070 (1.77) travel

Maximum Travel: .100 (2.54)

Working Travel: .070 (1.77)

MATERIALS

Receptacle: Nickel/silver,
gold lined inside

Spring: Music wire, gold plated

Plunger: Beryllium copper,
gold plated over nickel

HOW TO ORDER

R

SERIES

075

SIZE

J


TIP
STYLE

DE


PLATING
OPTION

LEAD FREE TEST PROBE

ICT-075-LF PROBE



STEEL PLUNGER TIP



PROBE SPECIFICATIONS

Minimum Centers: .075 (1.91)

Current Rating: 3 amps continuous

Spring Force: 7.0 oz. @ .170
(4.32) travel

Typical Resistance: < 40 mΩ
against a lead free surface

Maximum Travel: .250 (6.35)

Working Travel: .170 (4.32)

MATERIALS

Barrel: G2

Spring: Music wire, nickel plated

Plunger: Steel, Duralloy™ plated

HOW TO ORDER

ICT

SERIES

075

SIZE

LF

TIP
STYLE

7

SPRING
FORCE

D

PLATING
OPTIONS

S

STEEL
PLUNGER

Specifications subject to change without notice. Dimensions in inches (millimeters).



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

IDI:

[ICT-075-LF-7-D-S](#) [ICT-075-LF-10-D-S S/C](#)