

斯闊企業股份有限公司

S.SQUARE ENTERPRISE COMPANY,LTD.




普崙電子股份有限公司

PRO-WAVE ELECTRONICS CORPORATION

Model Number : 400FS080

Specification :




Resonant Frequency	40±1 KHz	Horizontal beam directivity	360°
Resonance Q	10	Vertical beam directivity	±40°
Bandwidth of 3 db	4 KHz	Driving voltage	150Vp-p for Burst
Maximum Sound Pressure Output	95 dB re 20 µPa @ 10 cm	Environmental Characteristics:	
Capacitance	1000 pF	Storage Temperature	-20℃ ~ +85℃
PVDF Thickness	30µm	Operating Temperature	+5℃ ~ +60℃




Unit: mm

Impedance Analyzer
HP 4192

Microphone Power Supply
B&K 2809



30Vp-p



10cm

Microphone
B&K 4939