

VHDCR-36-01-M-RA

VHDCP-68-01-M-EM

VHDCR, VHDCP SERIES

(0,80 mm) .0315"

VHDCI CONNECTORS

SPECIFICATIONS

For complete specifications and recommended PCB layouts see www.samtec.com?VHDCR or www.samtec.com?VHDCP

RoHS Compliant:

Yes


Lead-Free Solderable:

No

VHDCR Mates with:
VHDCP and Industry
Standard VHDCI
Cable Assemblies

VHDCP Mates with:
VHDCR

APPLICATION

Through-hole or
Edge MountRight Angle or
Edge Mount

36, 50 or 68 Positions

TYPE

VHDCR
= Right Angle

VHDCP
= Edge Mount

NO. OF POSITIONS

-36, -50, -68

01

PLATING


-M
= 15µ" (0,38µm) Gold

MOUNTING OPTION


-RA
= Right Angle
(Required for VHDCR)

-EM
= Edge Mount
(Required for VHDCP)



NO. OF POSITIONS	A VHDCR	B VHDCP
36	(29,90) 1.177	(21,80) .858
50	(35,50) 1.400	(27,40) 1.079
68	(42,70) 1.681	(34,60) 1.362



VHDCR



VHDCP



Note:
This Series is non-standard,
non-returnable.

Due to technical progress, all designs, specifications and components are subject to change without notice.

WWW.SAMTEC.COM

SAMTEC USA • Tel: +1-800-SAMTEC-9 or +1-812-944-6733 SAMTEC NORTHERN CALIFORNIA • Tel: +1-408-395-5900 SAMTEC SOUTHERN CALIFORNIA • Tel: +1-800-726-8329
 SAMTEC SOUTH AMERICA • Tel: +55 31 3786 3227 SAMTEC UNITED KINGDOM • Tel: +44 01236 739292 SAMTEC GERMANY • Tel: +49 (0) 89 / 89460-0
 SAMTEC FRANCE • Tel: +33 1 60 95 06 60 SAMTEC ITALY • Tel: +39 039 6890337 SAMTEC NORDIC/BALTIC • Tel: +46 8 4477280 SAMTEC BENELUX • Tel: +44 01236 739292
 SAMTEC ISRAEL • Tel: +972 3 7526600 SAMTEC INDIA • Tel: +91 80 3272 1612 SAMTEC ANZ • Tel: +613 9580 0683 SAMTEC SINGAPORE • Tel: +65 6745 5955 SAMTEC JAPAN • Tel: +81 45 475 1385
 SAMTEC SHANGHAI • Tel: +86 21 6083 3766 SAMTEC SHENZHEN • Tel: +86 755 83776780 SAMTEC TAIWAN • Tel: +886 2 2735 6109 SAMTEC HONG KONG • Tel: +852 26904658 SAMTEC KOREA • Tel: +82 31 717 5685