




NOTE:
TOLERANCE ON ALL TERMINALS TO BE ±.06

- MAX OPERATING VOLTAGE 29 VOLTS
- MAX PICKUP VOLTAGE 18 VOLTS
- MAX DROPOUT VOLTAGE 1-5 VOLTS
- RATED LOAD, RESISTIVE 600 AMPS
- COIL CURRENT 0.6 AMPS
- MIN OPERATING PERIOD 3 HRS
- MIN OPERATING CYCLES 50,000
- MAX WEIGHT 3 LB 7 OZ
- RATED DUTY CONTINUOUS
- NOMINAL COIL VOLTAGE 24-28 VOLTS
- AUX CONTACTS S.P.S.T. N.O.
- AUX CONTACT RATING 5 AMP 28 VOLTS

9	1	39529-001	OVERLAY				
8	4	51810-054	WASHER - LOCK NO.10 SPLIT				BRONZE
7	4	51807-084	WASHER - LOCK 3/8 SPLIT				BRONZE
6	2	51200-020	SCREW NO.4 x 1/4 PAN HD. SHT MET.				S.STEEL
5	4	50410-084	NUT NO.10-32 x 3/8 x 1/8 HEX				BRASS
4	4	50407-164	NUT 3/8-24 x 5/8 x 7/32 HEX				BRASS
3	1	16268-010	CONTACTOR ASSEMBLY-PRIMARY				
2	1	16043-001	PLATE - NAME				
1	1	09593-005	PLATE - BASE COVER				
FIND NO	QTY	PART OR IDENTIFYING NO	NOMENCLATURE OR DESCRIPTION	FSCM NO	DRAWING OR SPECIFICATION	MATERIAL OR NOTE	
UNLESS OTHERWISE SPECIFIED TOLERANCES ARE IN INCHES 10DECRA25 00							
2 PL DEC.13 PL DEC.1 ANGLES ±.06		±.010	±.1°				
			DR BY RLS	99/11/23			
			CHK BY RS	99/12/08			
			ENGR	99/12/08			
			MFG	99/12/10			
			RELEASE				
			CONTR NO.				
			GOVT APPVL				
				SIZE C	CODE IDENT 74063	DWG NO. A-712T	
				SCALE 1:2			
				SHEET			
HARTMAN ELECTRICAL MANUFACTURING MANFIELD, OHIO							
CONTACTOR - AIRCRAFT 600 AMP, CONTINUOUS DUTY							