

PART NAME	POTTING BOX (STYLE B)				PART No.	PB-1558-TF & PB-1559-TF / PB-1574-TF TO PB-1583-TF					REV. DATE	1-20-12																	
<u>MATERIAL:</u> ABS THERMOPLASTIC (CHI MEI POLYLAC PA-765) FLAMMABILITY RATING OF 94V-0 AT 0.070" THICKNESS AND CONTINUOUS USE TEMPERATURE OF 70° C.) <u>COLOR:</u> BLACK FINISH: OUTSIDE SURFACES ARE TEXTURED FINISH. COVER REDUCES INSIDE HEIGHT BY 0.075, EXCEPT ON PB-1577-TF COVER REDUCES INSIDE HEIGHT BY 0.060 & PB-1583-TF COVER REDUCES INSIDE HEIGHT BY 0.110. ALL COVERS HAVE SMOOTH SURFACES. LENGTH AND WIDTH DIMENSIONS ARE TAKEN FROM CLOSED END OF THE BOX. DIMENSIONS INCREASE SLIGHTLY AT OPEN END DUE TO TAPER. SHIPPED IN PACKAGES OF TEN (10). ALL DIMENSIONS HAVE ±0.010 TOLERANCE															0.187 DIA. HOLES QTY. (L) EXCEPT PB-1581-TF WHICH IS 0.156 DIA. 1°30' REF. EXCEPT PB-1579-TF WHICH IS 2° REF. INSERT AREA PB-1583-TF ONLY														
PART No.	A	B	C	D	E	F	G	H	J	K	L	M	N	OPTIONAL COVER															
PB-1558-TF	2.000	1.500	1.000	2.875	2.500	0.776	0.070	1.552	0.125	----	(2)	----	----	PBC-1558-CN															
PB-1559-TF	3.000	2.000	1.500	3.875	3.500	1.039	0.070	2.078	0.125	----	(2)	----	----	PBC-1575-C															
PB-1574-TF	2.000	2.000	1.500	2.875	2.500	1.039	0.070	2.078	0.125	----	(2)	----	----	PBC-1574-C															
PB-1575-TF	3.030	2.030	0.900	3.875	3.500	1.039	0.070	2.078	0.125	----	(2)	----	----	PBC-1575-C															
PB-1576-TF	3.000	3.000	1.500	3.875	3.500	1.539	0.070	3.078	0.125	----	(2)	----	----	PBC-1576-C															
PB-1577-TF	1.040	1.040	0.785	1.775	1.378	0.537	0.060	1.075	0.100	----	(2)	----	----	PBC-1577-C															
PB-1578-TF	4.000	2.125	2.000	4.875	4.500	1.115	0.070	2.230	0.125	----	(2)	3.790	1.906	PBC-1578-C															
PB-1579-TF	1.500	1.250	0.800	2.375	2.000	0.646	0.070	1.292	0.125	----	(2)	----	----	PBC-1579-C															
PB-1580-TF	4.000	1.750	1.000	4.875	4.500	0.901	0.070	1.802	0.125	----	(2)	----	----	PBC-1580-C															
PB-1581-TF	2.079	1.280	0.445	2.875	2.438	0.650	0.070	1.300	0.070	----	(2)	----	----	PBC-1581-C															
PB-1582-TF	4.063	2.188	0.900	4.875	4.500	1.115	0.070	2.230	0.125	----	(2)	----	----	PBC-1578-C															
PB-1583-TF	4.375	3.125	2.000	5.500	5.000	----	0.100	3.223	0.125	1.750	(4)	3.974	2.723	PBC-1583-C															

PART NAME	POTTING BOX (STYLE C)				PART No.	PB-1549-BF, PB-1558-BF PB-1574-BF, PB-1576-BF & PB-1577-BF					REV. DATE	1-26-11																	
<u>MATERIAL:</u> ABS THERMOPLASTIC (CHI MEI POLYLAC PA-765) FLAMMABILITY RATING OF 94V-0 AT 0.070" THICKNESS AND CONTINUOUS USE TEMPERATURE OF 70° C.) <u>COLOR:</u> BLACK <u>FINISH:</u> SMOOTH COVER REDUCES INSIDE HEIGHT BY 0.100 EXCEPT ON PB-1574-BF, PB-1576-BF & PB-1549-BF COVER REDUCES INSIDE HEIGHT BY 0.094. ON PB-1577-BF COVER REDUCES INSIDE HEIGHT BY 0.078. ALL COVERS HAVE SMOOTH SURFACES. SHIPPED IN PACKAGES OF TEN (10). ALL DIMENSIONS HAVE ±0.010 TOLERANCE															0.187 DIA. (2) HOLES K (TYP.)														
PART No.	A	B	C	D	E	F	G	H	J	K	OPTIONAL COVER																		
PB-1549-BF	3.050	3.050	0.875	4.000	3.500	1.538	3.324	0.125	0.085	0.082	PBC-1576-CN																		
PB-1558-BF	2.000	1.500	1.000	3.000	2.500	0.750	2.250	0.125	0.063	0.063	PBC-1558-C																		
PB-1574-BF	2.000	2.000	1.500	3.000	2.500	1.000	2.300	0.125	0.063	0.050	PBC-1574-CN																		
PB-1576-BF	3.000	3.000	1.500	4.000	3.500	1.500	3.300	0.125	0.094	0.050	PBC-1576-CN																		
PB-1577-BF	1.000	1.000	0.750	1.875	1.375	0.500	1.250	0.090	0.063	0.045	PBC-1577-CN																		