

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1120080013](#)
Status: **Active**
Overview: [Network Diagnostics Tools](#)
Description: NetMeter Hand Held Digital DeviceNet

Documents:
[Drawing \(PDF\)](#) [Product Literature \(PDF\)](#)
[RoHS Certificate of Compliance \(PDF\)](#)

General
Product Family Field Attachable / Accessories
Series [112008](#)
Approvals CE, CUL, UL certified
Comments NetMeter; Measures 667 Parameters, NetMeter;
Measures 667 Parameters
Communication Speed 125, 250, 500 Kbaud
I/O Connector 5-pole Micro-Change (M12)
IP Rating N/A
Material - Contact N/A
Overview [Network Diagnostics Tools](#)
Product Name DeviceNet, NetMeter
Type Hand Held Digital NetMeter®
UPC 78172506708

Physical
Cable Diameter N/A
Coupling Type N/A
Diagnostics / LEDs Yes
Diagnostics Port Yes
Gender N/A
Keyway N/A
Material - Connector Body N/A
Material - Coupling Nut N/A
Material - Plating Mating n/a
Net Weight 343.360/g
Orientation N/A
Poles N/A
Temperature Range - Operating 0°C to +40°C
Wire Size AWG N/A

Electrical
Current - Maximum per Contact N/A
Voltage - Maximum 7-30V DC

Material Info
Engineering Number DN-MTR

Reference - Drawing Numbers
Sales Drawing E-112008-0013-000



Series image - Reference only

EU ELV
Not Relevant

EU RoHS	China RoHS
Not Reviewed	
REACH SVHC	
Not Reviewed	
Halogen-Free	
Status	
Not Reviewed	
For more information, please visit Contact US	
China ROHS	Not Reviewed
ELV	Not Relevant
RoHS Phthalates	Not Reviewed

Search Parts in this Series
[112008](#) Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION