

**Ratings:**

|              |          |
|--------------|----------|
| Current      | 10A      |
| Voltage      | 300 V    |
| Wire Size    | 20-14AWG |
| Test Voltage | 2.0 kV   |

**Rated Cross Section:**

|                             |                    |
|-----------------------------|--------------------|
| Single Wire (solid)         | 1.5mm <sup>2</sup> |
| Stranded Wire (flexible)    | on request         |
| Stranded Wire with Ferrules | on request         |

**Dimensions:**

|                   |       |
|-------------------|-------|
| Spacing           | 5.0mm |
| PCB Hole Diameter | 1.0mm |
| Stripped Length   | 9.0mm |

**Materials:**

|                     |                 |
|---------------------|-----------------|
| Insulating Material | PA              |
| Flammability        | UL94V-0         |
| Temperature         | -30°C/+105°C    |
| Tension Spring      | Stainless Steel |
| Contact             | Cu              |
| Color               | Slade Gray      |

