


Shielded Cable Connector Kits (Continued)

Inner Ferrule on Jacket


No. of Positions	Cable Diameter (Less Than)
24	.300 7.62
36	.350 8.89
50	.400 10.16



Inner Ferrule on Braid*

No. of Positions	Cable Diameter (Greater Than)
24	.300 7.62
36	.350 8.89
50	.400 10.16

* Ferrule size based on braid bundle diameter



No. of Positions	Cable Range	Part Numbers						Cover Kits
		Shielded Plug Kit				Shielded Receptacle Kit		
		Screw Lock		Ball Lock		Screw or Ball Lock		
		B Slot	E Slot	B Slot	E Slot	B Slot	E Slot	
24	.250-.500 6.35-12.70	554948-4 ⁷ 554948-2 ⁶	554948-3 ⁴	—	554947-1	—	—	554944-1
36	.250-.500 6.35-12.70	554951-2	554951-1	554950-2	554950-1	—	5-554952-1 ⁵	554945-1
50	.350-.625 8.89-15.88	554954-2	554954-1	554953-2 ¹	554953-1 ¹	554955-2 ²	554955-1 ²	554946-1 ⁸ 554946-2

¹SCSI applicable.

²SCSI applicable with Hardware Kit Part Number 552561-6.

³For cable diameter of .500 [12.70] or less use -1 kit. For cable diameter greater than .500 [12.70] use -2 kit.


⁴Connector with M3.5 threads kits includes M3.5 x 2.00 [50.80] standoff stud.

⁵This kit available in bulk only.

⁶4-40 UNC-2B hole size.

⁷M3.5 x 0.6-6G, shoulder stud screws (2) supplied.

Typical Cable Assembly (Shielding Effectiveness)



For drawings, technical data, or samples contact your AMP sales engineer or call the AMP Product Information Center: 1-800-522-6752. Dimensions are in inches and millimeters unless otherwise specified. Values in brackets are metric equivalents. Specifications subject to change. Consult AMP for latest specifications.