


DC Power Jacks

163-4302-EX, 163-4303-EX

KOBICONN

DC Power Jacks



DIMENSIONS: In.

SPECIFICATIONS	
Pin Size (A):	$\phi 2\text{mm}$ (163-4302), $\phi 2.35$ (163-4303)
Contact Resistance:	30m Ω max.
Insulation Resistance:	100M Ω min. @ 250VDC
Breakdown Voltage:	250VAC for 1 minute
Rated Current:	0.5A @ 12/24V
Body:	ABS
Pin:	Nickel Plated Brass
Contact Spring:	Silver Plated Copper/Zinc/Aluminum Alloy
Terminals:	Silver Plated Brass
Insulator:	Phenol
Nut:	Polymid 12.5mm P=1
A:	163-4302 = $\phi .22 \times .084$ 163-4303 = $\phi .22 \times .10$
RoHS Compliant by Exemption	

Date Last Revised: 12-9-05

Available from Mouser Electronics
1-800-346-6873
www.mouser.com

KC-300842

163-4302-EX, 163-4303-EX

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Kobiconn:

[163-4303-EX](#) [163-4302-EX](#)