

5 - 8 Pin Cordsets

- IEC IP67 Protection



Connector Style	Female Part Number	Male Part Number	Features	Pinout	
BKM .. 	BKM 5-084-* BKWM 5-084-*	BSM 5-084-* BSWM 5-084-*	PVC Yellow, 5x18 AWG, 105°C, 300 VAC/VDC, 8 A, 7.0 mm OD, Cable #RF51084-*M†, 5-wire DC application, flexlife®	1. BN 2. WH 3. BU 4. BK 5. GY	Female Male
BKWM .. 	BKM 6-085-* BKWM 6-085-*	BSM 6-085-* BSWM 6-085-*	PVC Yellow, 6x18 AWG, 105°C, 300 VAC/VDC, 7 A, 7.5 mm OD, Cable #RF51085-*M†, 6-wire DC application, flexlife	1. BN 2. WH 3. BU 4. BK 5. GY 6. PK	Female Male
BSM .. 	BKM 7-086-* BKWM 7-086-*	BSM 7-086-* BSWM 7-086-*	PVC Yellow, 7x18 AWG, 105° C, 125 VAC/VDC, 7 A, 7.5 mm OD, Cable #RF51086-*M†, 7-wire DC application, flexlife	1. WH 2. BN 3. GN 4. YE 5. GY 6. PK 7. BU	Female Male
BSWM .. 	BKM 8-087-* BKWM 8-087-*	BSM 8-087-* BSWM 8-087-*	PVC Yellow, 8x18 AWG, 105° C, 125 VAC/VDC, 7 A, 8.5 mm OD, Cable #RF51087-*M†, 8-wire DC application, flexlife	1. WH 2. BN 3. GN 4. YE 5. GY 6. PK 7. BU 8. RD	Female Male

* Length in meters. Standard cable lengths are 5 and 10 meters. Consult factory for other lengths.

Standard housing and coupling nut material is anodized aluminum.. "BKM.."; "BKMV.." indicates stainless steel and "BKMK.." indicates nylon.

† See Section N for **reelfast**® cable information.