





	1	2	3	4	5	6	7		
A	    Material Terminal body (contact pin): Brass(CuZn) Tin plated Insulator (housing): Thermoplastic (UL94V-0),Green Electrical cULus/ CSA /VDE Voltage rating: 300VAC/125VAC/125VAC Current rating: 10A/8A/10.5A Wire range: Solid wire(AWG): Stranded wire(AWG): Withstanding Voltage: 1.6KV/1.6KV/2.5KV Operating temperature: -30°C to +105°C Soldering temperature: 250°C±10°C/5 Sec Safety Approval:  N= NUMBER OF CONTACTS							A	
B								B	
C								C	
D								D	
E								E	
F								F	
G	RoHS compliant		Scale 1:1		Date		Name	Customer-No.	G
TOLERANCE			Drawn		10.12.2009	Dean	ASSMANN WSW-No. A-TB350-OQxxCV		
			X. ±0.50		Approved		10.12.2009	Hellwig	
			X.X ±0.30						
			X.XX ±0.10						
H			DIM TOL				Drawing-No.		
			X.° ±1°				ASS 3819 CO		rev01
			Angle TOL		① Drawn		10.12.2009	Dean	
					Id.		Modification	Date	Name
	1	2	3	4	5	6	7		