




WRAPOST RECEPTACLES
for .022" - .032" diameter pins (#06 contact)
and .022" - .034" diameter pins (#16 contact)




2297



2297-X-17-XX-16-XX-02-0
Press-fit in .067 mounting hole

Basic Part Number	# of Wraps	Length A
2297-2	2	.370
2297-3	3	.430


0280



0280-X-17-XX-06-XX-02-0
Press-fit in .081 mounting hole

Basic Part Number	# of Wraps	Length A
0280-2	2	.360
0280-3	3	.510

0281



0281-3-17-XX-06-XX-02-0
Press-fit in .080 mounting hole

SPECIFICATIONS

SHELL MATERIAL:
Brass Alloy 360, 1/2 Hard

CONTACT MATERIAL:
Beryllium Copper Alloy 172, HT

DIMENSION IN INCHES
TOLERANCES ON:
LENGTHS: ±.005
DIAMETERS: ±.002
ANGLES: ± 2°

ORDER CODE: XXXX - X - 17 - XX - XX - XX - 02 - 0

BASIC PART #

SPECIFY SHELL FINISH:

- 01 200μ" TIN/LEAD OVER NICKEL
- ◇ 80 200μ" TIN OVER NICKEL (RoHS)
- ◇ 15 10μ" GOLD OVER NICKEL (RoHS)



SPECIFY CONTACT FINISH:

- 01 200μ" TIN/LEAD OVER NICKEL
- ◇ 80 200μ" TIN OVER NICKEL (RoHS)
- ◇ 27 30μ" GOLD OVER NICKEL (RoHS)

SELECT CONTACT

#06 or #16 CONTACT (DATA ON PAGES 221 & 222)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Mill-Max:

[0281-3-17-01-06-27-02-0](#) [2297-2-17-01-16-01-02-0](#)