

Pushbutton Units and Indicator Lights

30 mm Heavy Duty, Watertight/Oiltight, Class 52

Pushbutton operators only

Selection and ordering data

Version	Color of actuator	Order no.	Pack
			nit
Pushbutton with flush cap	black red green yellow blue gray orange less cap kit with all colors	52PA8A1 52PA8A2 52PA8A3 52PA8A4 52PA8A5 52PA8A6 52PA8A8 52PA8 52PA8AN	1
Pushbutton with extended cap	black red green yellow blue gray orange less cap kit with all colors	52PA8B1 52PA8B2 52PA8B3 52PA8B4 52PA8B5 52PA8B6 52PA8B8 52PA8 52PA8BN	1
Pushbutton with mushroom cap 1 5/8" (41.3mm)	black red green yellow blue gray orange less cap kit with all colors	52PB9D1 52PB9D2 52PB9D3 52PB9D4 52PB9D5 52PB9D6 52PB9D8 52PB9 52PB9DN	1
Pushbutton with mushroom cap 2 1/2" (63.5mm)	black red green yellow blue gray orange less cap less cap with lens kit	52PB9E1 52PB9E2 52PB9E3 52PB9E4 52PB9E5 52PB9E6 52PB9E8 52PB9 52PB9EN	1
2 position push pull maintained, non illuminated			
Metal Mushroom Head, 1 5/8" (41.3 mm)	red green chrome	52PA2A2 52PA2A3 52PA2AC	1
Small Plastic Mushroom Head, 1 5/8" (41.3 mm)	black red green	52PA2W1 52PA2W2 52PA2W3	1
Large Plastic Mushroom Head, 2 1/4" (57.2 mm)	black red green	52PA2V1 52PA2V2 52PA2V3	1

Flush pushbutton operator



2 position push pull operator



Pushbutton Units and Indicator Lights

30 mm Heavy Duty, Watertight/Oiltight, Class 52

Push to test units

Selection and ordering data


	Version	Color of actuator	Contact blocks	Order no. Operators with Incandescent lamp	List Price \$	Order no. Operators with LED lamp		Pack
Push to test/illuminated pushbutton  52PA6D2A	Illuminated pushbuttons/Push to test indicator light with plastic lens - Full voltage type AC/DC ¹⁾							
	6-8V with 755 type	red	1NO + 1NC	52PA6B2A	90.40	52PE6B2A	1	
		green	1NO + 1NC	52PA6B3A	90.40	52PE6B3A		
		amber	1NO + 1NC	52PA6B9A	90.40	52PE6B9A		
		less lens	1NO + 1NC	52PA6BNA	85.00	— ²⁾		
	24V with 757 type	red	1NO + 1NC	52PA6D2A	90.40	52PE6D2A	1	
		green	1NO + 1NC	52PA6D3A	90.40	52PE6D3A		
		amber	1NO + 1NC	52PA6D9A	90.40	52PE6D9A		
		less lens	1NO + 1NC	52PA6DNA	85.00	— ²⁾		
	 52PA6G2A	Illuminated pushbuttons/Push to test indicator light with plastic lens - Transformer type AC/DC ¹⁾						
120V with 6V 755 type lamp		red	1NC + 1NO	52PA6G2A	105.40	52PE6G2A	1	
		green	1NC + 1NO	52PA6G3A	105.40	52PE6G3A		
		amber	1NC + 1NO	52PA6G9A	105.40	52PE6G9A		
		less lens	1NC + 1NO	52PA6GNA	100.00	— ²⁾		
240V with 6V 755 type lamp		red	1NC + 1NO	52PA6H2A	105.40	52PE6H2A	1	
		green	1NC + 1NO	52PA6H3A	105.40	52PE6H3A		
		amber	1NC + 1NO	52PA6H9A	105.40	52PE6H9A		
		less lens	1NC + 1NO	52PA6HNA	100.00	— ²⁾		
480V with 6V 755 type lamp		red	1NC + 1NO	52PA6J2A	105.40	52PE6J2A	1	
		green	1NC + 1NO	52PA6J3A	105.40	52PE6J3A		
		amber	1NC + 1NO	52PA6J9A	105.40	52PE6J9A		
		less lens	1NC + 1NO	52PA6JNA	100.00	— ²⁾		
600V with 6V 755 type lamp		red	1NC + 1NO	52PA6K2A	105.40	52PE6K2A	1	
		green	1NC + 1NO	52PA6K3A	105.40	52PE6K3A		
		amber	1NC + 1NO	52PA6K9A	105.40	52PE6K9A		
		less lens	1NC + 1NO	52PA6KNA	100.00	— ²⁾		
Push to test indicator light with plastic lens - Resistor type AC/DC								
120V with 24V 757 type lamp	red	1NC + 1NO	52PA6M2A	90.40	52PE6M2A	1		
	green	1NC + 1NO	52PA6M3A	90.40	52PE6M3A			
	amber	1NC + 1NO	52PA6M9A	90.40	52PE6M9A			
	less lens	1NC + 1NO	52PA6MNA	85.00	— ²⁾			
240V with 24V 757 type lamp	red	1NC + 1NO	52PA6N2A	90.40	52PE6N2A	1		
	green	1NC + 1NO	52PA6N3A	90.40	52PE6N3A			
	amber	1NC + 1NO	52PA6N9A	90.40	52PE6N9A			
	less lens	1NC + 1NO	52PA6NNA	85.00	— ²⁾			
Color code table: blue clear white				5 A B		5 A B		

Color code table: blue
clear
white

5
A
B

5
A
B

Wiring Diagrams



1) All illuminated devices come with std. Touch-safe shield per UL stds.

2) LED color must match lens color. Consult Factory for Neon types.