








SF 3020	Rated Current A	Leakage Current @ 250V 50Hz	Inductance mH	Connections	Approvals	UL	CSA	SE
Standard Version								
SF 3020-1/08	1	0.2mA	7	PCB Pins	☒	☒	☒	☒
SF 3020-3/08	3	0.2mA	2	PCB Pins	☒	☒	☒	☒
SF 3020-6/08	6	0.2mA	0.9	PCB Pins	☒	☒	☒	☒
Medical Version								
SF 3020M-1/08	1	5µA	7	PCB Pins	☒	☒	☒	☒
SF 3020M-3/08	3	5µA	2	PCB Pins	☒	☒	☒	☒
SF 3020M-6/08	6	5µA	0.9	PCB Pins	☒	☒	☒	☒

Temperature Range: -25°C to +85°C

Operating Voltage: 250Vac


Operating Frequency: 0 to 400Hz

Test Voltage: L+N to ground 2700Vdc, 2 seconds

☒ Approved
☐ Submitted for Approval


DIMENSIONS

All dimensions are nominal and in mm




CIRCUIT DIAGRAMS

Standard Version



Medical Version (Suffix 'M')



PIN CONNECTIONS

