

| REV. | DESCRIPTION | DATE       |
|------|-------------|------------|
| A    | RELEASE     | 2012.11.12 |






NOTES:  
Insulator Material: PBT, UL 94V-0  
Contact Plating: Flash Gold  
Contact Material: Brass

Current Rating : 1A AC,DC  
Contact Resistance: 20mΩ Max.  
Dielectric Withstanding: AC 500V  
Insulator Resistance: 1000MΩ Min.  
Operating Temp.: -40°C~+105°C

| NUMBER<br>OF POSITIONS | DIMENSIONS |       |
|------------------------|------------|-------|
|                        | A          | B     |
| 06                     | 4.00       | 21.60 |
| 08                     | 6.00       | 23.60 |
| 10                     | 8.00       | 25.60 |
| 12                     | 10.00      | 27.60 |
| 14                     | 12.00      | 29.60 |
| 16                     | 14.00      | 31.60 |
| 20                     | 18.00      | 35.60 |
| 24                     | 22.00      | 39.60 |
| 26                     | 24.00      | 41.60 |
| 30                     | 28.00      | 45.60 |
| 34                     | 32.00      | 49.60 |
| 40                     | 38.00      | 55.60 |
| 44                     | 42.00      | 59.60 |
| 50                     | 48.00      | 65.60 |
| 60                     | 58.00      | 75.60 |



| UNLESS TOLERANCE |             | DRAW         | BY   |
|------------------|-------------|--------------|------|
| GENERAL          | ANGLE       | DESIGN       | BY   |
| X. ± 0.30°       | X.° ± 3.0°  | CHECK        | BY   |
| .X ± 0.20        | .X° ± 2.0°  | APPROVE      | BY   |
| .XX ± 0.15       | .XX° ± 1.0° | CnC Tech,LLC |      |
| .XXX ± 0.08      | .XXX ± 0.5° |              |      |
| SCALE            |             | SHEET        | UNIT |
| 1:1              |             | 1/1          | MM   |
| DRAW NO:         |             | REV: A       |      |



A

B

C

D

A

B

C

D