


REV.	DATE	ECR NO.	DESCRIPTION
NC	05/30/00	—	INITIAL RELEASE
NC	04/30/08	100012	UPDATE DRAWING FORMAT



NOTES:

1. CRIMPED FERRULE HEX CRIMP SIZE .213"

					UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY. UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 – 8mm ± 0.20mm 8 – 30mm ± 0.40mm 30 – 120mm ± 0.50mm UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 – .315 = ± 0.007” .315 – 1.180 = ± 0.015” 1.180 – 4.724 = ± 0.020” DO NOT SCALE DRAWING	APPROVALS		DATE		Amphenol Connex							
8						DRAWN	GRS	04/30/08									
7	FERRULE	COPPER	GOLD	1		CHECKED											
6	HEX NUT	BRASS	GOLD	1		ISSUED				PART DESCRIPTION SMA BULKHEAD CRIMP JACK O-RING SEAL (FOR RG-142/U, 223/U, 400/U CABLE)							
5	LOCK WASHER	BRASS	GOLD	1		SHEET	1 OF 1										
4	GASKET	SILICONE	RED	1													
3	CONTACT PIN	BER. COPPER	GOLD	1				PART NO. 132281									
2	INSULATOR	PTFE	NATURAL	1													
1	BODY	BRASS	GOLD	1													
	DESCRIPTION	MATERIAL	FINISH	QTY			CAD FILE C:/132/132281.DWG		DWG. NO.		132281.DWG		REV.	A	SIZE	A	SCALE