


LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
AJ	16		A1	REVISED PER ECO-11-005030	11MAR11	RK	HMR

D


C

B

A



RECOMMENDED PANEL CUTOUT



RECOMMENDED STRIP LENGTH

- 1 MAX PANEL THICKNESS .240.
- 2 USE WITH PRO-CRIMPER 354940-1.
- 3. USE INSTRUCTION SHEET 408-9763.
- 4 BULK KIT PACKAGE, 100 PER BAG.

4	CUSTOM CABLE	—	—	—	222001-6	227194-2	329633	1-329631-2	1-329632-2	9-413658-2	1-413746-0	413744-2	2-5413590-1		
	AT&T 735A	4.52 [.178]	1.07 [.042]	58425-2	—	—	329633	1-329631-2	1-329632-2	9-413658-2	1-413746-0	413744-2	1-5413590-8		
	CUSTOM CABLE, C/C-24AWG, DOD-.109, JOD-.153	4.52 [.178]	1.07 [.042]	58425-2	—	—	329633	1-329631-2	1-329632-2	9-221132-6	413746-5	413744-2	1-5413590-7		
	RG-179/U & 187/U	4.52 [.178]	1.07 [.042]	58425-2	222001-6	227194-2	329633	1-329631-2	1-329632-2	9-413658-0	1-413746-5	413744-2	5413590-8		
	AT&T KS 19224 L2 AND JIS 1.5C-XV	4.52 [.178]	1.07 [.042]	58425-2	222001-6	227194-2	329633	1-329631-2	1-329632-2	9-413658-2	1-413746-5	413744-2	5413590-4		
	BELDEN 8218 AND JIS 2.5C-2V	4.52 [.178]	1.07 [.042]	58425-2	—	—	329633	1-329631-2	1-329632-2	9-221132-6	1-413746-0	413744-2	5413590-3		
FOR USE WITH CABLE		FERRULE (HEX)	CONTACT (SQ)	DIE SET	8 TUBING, METAL QTY=1	7 TUBING, PLASTIC QTY=1	6 GASKET QTY=1	5 JAM NUT QTY=1	4 LOCKWASHER QTY=1	3 FERRULE QTY=1	2 CONTACT QTY=1	1 JACK ASSY QTY=1	PART NUMBER		
		CRIMP HEIGHTS													
THIS DRAWING IS A CONTROLLED DOCUMENT.															
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		DWN L. VARELA - 22APR2005		CHK J. HAVENER - 22APR2005		NAME							
		0 PLC ± - 1 PLC ± - 2 PLC ± 0.41 [0.16] 3 PLC ± - 4 PLC ± - ANGLES ± -		APVD J. LIPPERT - 22APR2005		PRODUCT SPEC									
				APPLICATION SPEC		JACK, BULKHEAD, 75 OHM, HEX CRIMP, BNC									
MATERIAL		FINISH		WEIGHT		SIZE		CAGE CODE		DRAWING NO		RESTRICTED TO			
—		—		—		A1		00779		C=5413590		—			
CUSTOMER DRAWING										SCALE 5:1		SHEET 1 OF 1		REV A1	