



1


2

3

4



A



B

TIN LEAD PART NUMBER					
SHELL	A±0.38	B±0.12	C±0.10	D±0.25	PART NUMBER
09	30.81	24.99	16.96	16.21	10.96 D09S24A.GX00
15	39.14	33.32	25.18	24.54	19.18 D15S24A.GX00
25	53.03	47.04	39.12	38.25	33.12 D25S24A.GX00
37	69.32	63.50	55.68	54.71	49.68 D37S24A.GX00

C

Plating: 4 --> flash AU
Plating: 6 --> 0.76µ AU


LEAD FREE PART NUMBER					
SHELL	A±0.38	B±0.12	C±0.10	D±0.25	PART NUMBER
09	30.81	24.99	16.96	16.21	10.96 D09S24A.GX00LF
15	39.14	33.32	25.18	24.54	19.18 D15S24A.GX00LF
25	53.03	47.04	39.12	38.25	33.12 D25S24A.GX00LF
37	69.32	63.50	55.68	54.71	49.68 D37S24A.GX00LF

D

Plating: 4 --> flash AU
Plating: 6 --> 0.76µ AU

rev	ecn no	dr	date
B	-	JAR	1999/10/18
D	LS05-001	MPE	2005/03/14
E	LS05-0056	MPE	2005/06/28
F	LS06-0019	LGO	2006/02/07
G	LS06-0097	LGO	2006/07/28
H	110-0059	NG	2010-02-23
-	-	-	-

GENERAL CHARACTERISTICS AND ROHS INFORMATIONS:
SEE DRAWING C01-8646-0000



PC card drilling dimensions(after plating)
(thickness 1.60±0.20mm)

B

www.fciconnect.com		surface	ISO 1302	tolerance std	ISO 406 ISO 1101	projection	mm
		TOLERANCES UNLESS OTHERWISE SPECIFIED		TOLERANCES UNLESS OTHERWISE SPECIFIED		projection	
Dr	JOUBERT	1996/09/10	ANGULAR	0.X	±0.1	size	A3
Eng	PESSON	1996/09/10	LINEAR	0.XX	±0.1	size	A3
Chr	NIRMAL GEORGE	2010-02-23	0.XX	±2	±0.1	ECN	110-0059
Appr	SUDHIR VARMA	2010-02-23	Product family		D-SUB		Spec ref -
FEMALE CONNECTOR STD EURO		straight solder type for		C01-8646-0495		Rev.	
catalog no		-		CUSTOMER		sheet 1 of 1	

D

European Views



Copyright FCI.