

HC-D 25-SD-FL/FS

Order No.: 1660135

<http://eshop.phoenixcontact.de/phoenix/treeViewClick.do?UID=1660135>

HEAVYCON protective cover, type D25, for supporting base element with single locking latch, with retaining cord, IP54, PA

Commercial data

GTIN (EAN)	
sales group	D093
Pack	10 pcs.
Customs tariff	39269097
Catalog page information	Page 550 (PC-2009)

Product notes

WEEE/RoHS-compliant since:
03/01/2006



<http://www.download.phoenixcontact.com>
Please note that the data given here has been taken from the online catalog. For comprehensive information and data, please refer to the user documentation. The General Terms and Conditions of Use apply to Internet downloads.

Technical data

General data

Design	D25
Type	For supporting base element with single locking latch
Locking type	for single locking latch
Degree of protection	IP54
Ambient temperature (operation)	-20 °C ... 100 °C

Seal material	NBR
Material, protective cover	PA
Inflammability class acc. to UL 94	HB
Connection	Plastic protective cover for short-term protection

Certificates / Approvals



Certification

GOST

Address

PHOENIX CONTACT Inc., USA
586 Fulling Mill Road
Middletown, PA 17057, USA
Phone (800) 888-7388
Fax (717) 944-1625
<http://www.phoenixcon.com>



© 2010 Phoenix Contact
Technical modifications reserved;