

(2,54mm) .100"

CLH SERIES

# SMT LOW PROFILE SOCKET

## SPECIFICATIONS

For complete specifications and recommended PCB layouts see [www.samtec.com?CLH](http://www.samtec.com?CLH)

### Insulator Material:

Black Liquid  
Crystal Polymer

### Contact Material:

Phosphor Bronze

### Operating Temp Range:

-65°C to +125°C with Gold

-65°C to +105°C with Tin

### Plating:

Au or Sn over

50µ" (1,27µm) Ni

### Contact Resistance:

10 mΩ max

### Insertion Depth:

(2,67mm) .105" to

(3,43mm) .135"

plug from top, (3,18mm) .125"  
min plus board thickness plug  
from bottom

### Insertion Force:

4.0oz (1,11N) average

### Normal Force:

50 grams (0,48N)

### Withdrawal Force:

1.1oz (0,31N) average

### Max Cycles:

100 with 10µ" (0,25µm) Au

### RoHS Compliant:

Yes

### Processing:

Lead-Free Solderable:

Yes

### SMT Lead Coplanarity:

(0,10mm) .004" max



**Mates with:**  
TSW, MTSW, HW, DW,  
EW, ZW, TLW, TSM,  
MTLW

CLH

1

NO. PINS  
PER ROWPLATING  
OPTION

D


ENTRY  
OPTIONOTHER  
OPTION

—DV  
= Top  
Entry

—BE  
= Bottom  
Entry


—K  
= (6,50mm) .256"  
DIA Polyimide film  
Pick & Place Pad  
(3 positions min.)

—P  
= Pick & Place Pad  
(3 positions  
minimum)




Not always necessary  
for auto placement.  
Call Samtec.

—A  
= Alignment Pin  
(4 positions  
minimum)



—LC  
= Locking  
Clip



—TR  
= Tape & Reel  
Packaging  
(29 positions  
maximum)

CLH-108-F-D-DV-P




CLH-120-F-D-BE



CLH-110-F-D-DV



02 thru 50



**Note:** Some lengths,  
styles and options are  
non-standard, non-returnable.

Due to technical progress, all designs, specifications and components are subject to change without notice.

[WWW.SAMTEC.COM](http://WWW.SAMTEC.COM)

SAMTEC USA • Tel: 1-800-SAMTEC-9 or 812-944-6733 SAMTEC SILICON VALLEY • Tel: 408-395-5900 SAMTEC SOUTHERN CALIFORNIA • Tel: 1-800-726-8329  
SAMTEC AMERICA LATINA COMERCIO EXTERIOR LTDA • Tel: (+55 31) 3786 3227 SAMTEC UNITED KINGDOM • Tel: 44 01236 739292 SAMTEC GERMANY • Tel: +49 (0) 89 / 89460-0  
SAMTEC FRANCE • Tel: 33 01 60 95 06 60 SAMTEC ITALY • Tel: 39 039 6890337 SAMTEC NORDIC/BALTIC • Tel: +46-84477280 SAMTEC BENELUX • Tel: 44 01236 739292 SAMTEC ISRAEL • Tel: 972-3-7526600  
SAMTEC INDIA • Tel: +91-80-3272 1612 SAMTEC ASIA PACIFIC • Tel: 65 6745-5955 SAMTEC JAPAN • Tel: 045-475-1385 SAMTEC CHINA • Tel: 86-21-61103766 SAMTEC TAIWAN • Tel: 886-2-2735-6109  
SAMTEC HONG KONG • Tel: 852-26904858 SAMTEC KOREA • Tel: 82-31-717-5685 SAMTEC ANZ • Tel: 613 9512 7747 SAMTEC SOUTH AFRICA • Tel: 27 11 452 8112