


2.5mm Four Conductor Phone Jack

KOBICONN

161-2828

2.5mm Four Conductor Phone Jack



Dimensions: mm (In.)

Specifications	
Contact Resistance:	30mΩ Max.
Unspecified Tolerance:	dimension shall be ± 0.3mm
Insulation Resistance:	100MΩ min. @ 500VDC
Dielectric Strength:	500 VAC for one minute
Insertion and Extraction Force:	4 to 20 N
Body:	PA Black
Cover Terminal:	gold plated copper
Terminals:	silver plated copper
Life Cycle:	5,000 cycles min.

Date Last Revised: 10-14-05

Available from Mouser Electronics
1-800-346-6873
www.mouser.com

KC-300159

161-2828

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Kobiconn:](#)

[161-2828](#)