


.025 ± .002 (1/16A-10A)
.032 ± .002 (12A-15A)



NOTES:

1. UL RECOGNIZED THRU 15A & CSA CERTIFIED.
INTERRUPTING CAPACITY TO 300A DC AT 125V,
50A AC AT 125V
2. MATERIALS:
BODY - GLASS
COATING - INSULATING EPOXY
LEADS - SOLDER COATED COPPER
3. TO BE STAMPED WITH L/F & AMPERAGE
ON 2 OPPOSITE SIDES.

ELECTRICAL CHARACTERISTICS			
% OF AMPERAGE RATING	CLEARING TIME 7A & LOWER	CLEARING TIME 10A	CLEARING TIME 12A & HIGHER
100%	4 HRS. MIN.	4 HRS. MIN.	4 HRS. MIN.
200%	1 SEC. MAX.	3 SEC. MAX.	10 SEC. MAX.

NO	COMPONENT NO	DESCRIPTION	QTY	U/M
BILL OF MATERIAL				
COPIES TO		MATL SPEC	SEE NOTE 2	FINISH
LTR	1	9	18	
	37485D	DRW	BJJ	DATE 6/11/96
		2	10	SCALE 2:1
		3	12	
		4	20	CHK SUPER DRW
		4	13	21
		5	14	23
		6	15	33
		7	16	43
		8	17	53
TITLE		TOLERANCE UNLESS OTHERWISE SPECIFIED TWO PLACE DEC. +.01 THREE PLACE DEC. ±.005 ANGULAR ±1°		
 REVISION DES PLAINES, ILL INOIS 60016 0252000				
CHK	APD	REWORK	DRWA	NO
PICO II				OUTLINE

Ⓢ DENOTES CPK DIMENSIONS. -MINIMUM CPK VALUE

CONTROLLED DOCUMENT