





JKL PART NUMBER	COLOR	STARTING CIRCUIT VOLTAGE VS (Vrms)	OPERATING LAMP VOLTAGE VL (Vrms)	OPERATING LAMP CURRENT IL (mArms)	BRIGHTNESS (CANDELA/m2)	*RATED LIFE (HRS) TYPICAL
BF22258-25B	LCD HIGH OUTPUT WHITE 9700°k RGB	1600 @ 0°C	535	5 ± 1	38,000 ±10%	50,000

* RATED LIFE IS DEFINED AS THE POINT AT WHICH THE INTENSITY BECOMES 50% OF THE INITIAL RATING.

			METRIC	DIMENSIONS ARE IN MILLIMETERS	JKL COMPONENTS CORPORATION			
REV. NO.	DESCRIPTION/ECO NUMBER	APPV'D DATE	THIRD ANGLE PROJECTION	TOLERANCE UNLESS OTHERWISE SPECIFIED 1 PL +/- 0.2 2 PL +/- 0 ANGLE +/- 0	TITLE	SIZE	FSCM NO.	DRAWING NO.
F	RATED LIFE HRS. TYPICAL & 20,000 TO 50,000	8/19/09		DRAWN BY L. WENGSTROM APPV'D BY L.R. DATE 8/19/09	MINIATURE COLD CATHODE FLUORESCENT LAMP	A	55335	BF22258-25B
E	ADD MINIMUM TO RATED LIFE HRS.	7/16/09						
D	CHANGE ON ELECT. CHART	4/16/09						
C	CHANGE ON CIRCUIT & LAMP VOLTAGE	7/19/04						
B	CHANGE ON OUTPUT RGB	11/11/02						
A	NEW CHART	6/5/01						
	RELEASED	6/4/01						
			- CAD DRAWING -		SCALE	NONE		
			MANUAL REVISIONS NOT PERMITTED		RELEASED DATE	6/4/01	REVISION DATE	8/19/09
					REV. NO.	F		SHEET 1 OF 1