


Dimensions: mm (in.)

**Electrical Specifications:**

- Rating: 0.5A/125VAC
- Contact Resistance: 20mΩ @ 2.5VDC and 1A or less
- Insulation Resistance: 100MΩ @ 500VDC for more
- Dielectric Strength: 1,000VAC for 1 minute

Mechanical Specifications:

- Circuit: SPST Off-(On)
- Operating Temperature: -10°C to +55°C

Materials:

- Terminal: Gold plated sterling silver plate
- Spring Washer: Nickel plated steel/ copper plate
- Hex Nut: Nickel plated nickel sheet
- Shaft: ABS
- Body: Phenolresin, Black
- Button: 10PA018 (red); 10PA019 (black)

Soldering Process:

- Temperature: 270°C within 3 sec.
- Note: Recommended for hand soldering only

Pushbutton Switches
10PA018, 10PA019

Mountain
Switch

Available from Mouser Electronics

www.mouser.com

1-800-346-6873

Specifications are subject to change without notice. No liability or warranty implied by this information. Environmental compliance based on producer documentation.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Mountain Switch:](#)

[10PA018](#) [10PA019](#)