


Rail Mounted Terminal Blocks

9123140000

When good enough just isn't good enough

Weidmüller 

ASK 1 LD

[Email to a Friend](#)[View Catalog Page](#)

Representative Photo

Technical Information

Clamping Type	Screw Clamp
Series	SAK Series W Series
Rail Type	Combi Foot
Function	Circuit Protection
Configuration	Single Level
Wire Size	#22...12 AWG
Current	10 A
Voltage	300 V
Color/Material	Beige PA
Special Requirements	Blown fuse indication 24 VDC Hinge (+), 5 x 20 mm fuse

Technical Data

	UL	CSA	VDE
Rated Voltage	300 V	300 V	500 V
Rated Current	10.0 A	10.0 A	
Wire Size	#22...12 AWG	#26...12 AWG	4 mm ²

Additional Data

Width/Length/Height mm (in.)	8/58/44 (.31"/2.28"/1.73")
Insulation Stripping Length mm (in.)	9 (.35")
Torque Nm (lb. in)	0.9 (8.0)
Clamping Screw	M 3
Flammability Class	UL 94 (V2)

Suggested Accessories

DIN-rail

End bracket

End plate/partition (AP/TW)

Ferrules

Fuses

Markers (SchT)

Marking pens

Marking tags (DEK)

Mounting brackets

Tools

Product Liability The above information describes our products. It does not constitute guaranteed properties and is not intended to affirm the suitability of a product for a particular application. Regrettably, omissions and exceptions cannot be completely ruled out. Technical data are always specified by their average values. Exact data and the tolerances which apply to our processes can be requested from:

Weidmüller - North America

United States 001 (800) 849-9343

Canada 001 (800) 268-4080

or

Weidmüller - Germany

Telephone operator 0049 (-5252) 960-0