



B

CONTINUOUS HINGES

長蝶番

平蝶番

裏蝶番

抜き差し蝶番

段付蝶番

クリーンヒンジ

特装車蝶番

フリーザーヒンジ

特殊蝶番

トルクヒンジ

ステー

周辺機器(B)

MS-20001 長蝶番

米国軍用規格長蝶番(MS規格)

MILITARY STANDARD CONTINUOUS HINGES



輸入品

MS-20001
アルミニウム製

特徴 Feature

- アルミ押出し材のため、軽量で強度があります。
- MS規格適合品
- 加工性に優れています。

- Thanks to aluminum extrusion, this is lightweight and large strength.
- Conformity to MS standard.
- Easy machinable.

仕様 ●材質: アルミニウム合金押出し材
(軸はステンレス製)

用途 ●表面仕上: アルマイト処理
●通信機器・測定機器・船舶・車両・小型コンテナなどの筐体

納期 ●標準品・・・納期お問合ください
備考 ●輸入品のため色が異なることがあります。
●航空機にはMS規格品をご使用ください。
●軸の抜け止め加工はしていません。蝶番を必要寸法に切断後軸にカシメ等の抜け止め加工をしてご使用ください。
●両端に抜け止め加工を行う場合は、必ず同じ羽根で行ってください。異なる羽根で行うと作動不良の原因となります。

Specifications ●Material: Aluminum alloy extrusion.
(Shaft: Stainless steel)

●Finish: Alumite treatment


Specific-use ●Cases for aircraft, communication equipment, measuring equipment, ships, vehicles and small containers.

Remarks ●A color is sometimes different for the imports.
●The MS (Military Standard) articles must be used for the air crafts.

●The hinge is not processed to prevent extraction of the shaft. After cutting the hinge to size and before use, fix stops, etc., on the shaft to prevent its extraction.
●When fixing stops on both ends, always fix on the same wing. Fixing on different wings may cause faulty operation.


MS-20001-P3

MS-20001-P8



軸はステンレス製です。
Shaft is made of stainless steel ●長尺商品のため、送料が掛かります。詳細はお問合ください。

軽飛行機の内装に軽量で丈夫です。
Lightweight and durable for light airplane interior.



商品番号 Product No.	RoHS	CAD	W ₁	W ₂	t		φD ₁	φD ₂		R	製品質量(g) Mass	コード Code	単価 Price	量販価格 Bulk Price	
					MAX.	MIN.		MAX.	MIN.					数量 Quantity	単価 Price
MS-20001-P2			1 1/16(27.0)	0.135(3.4)	0.056(1.4)	0.044(1.1)	0.089(2.3)	0.187(4.7)	0.173(4.4)	0.174(4.4)	280	12446	価格はお問合ください		
MS-20001-P3			1 1/4(31.8)	0.135(3.4)	0.056(1.4)	0.044(1.1)	0.089(2.3)	0.187(4.7)	0.173(4.4)	0.174(4.4)	300	12447			
MS-20001-P4			1 1/2(38.1)	0.135(3.4)	0.056(1.4)	0.044(1.1)	0.089(2.3)	0.187(4.7)	0.173(4.4)	0.174(4.4)	365	12448			
MS-20001-P6			2 (50.8)	0.135(3.4)	0.056(1.4)	0.044(1.1)	0.089(2.3)	0.187(4.7)	0.187(4.7)	0.174(4.4)	415	12450			
MS-20001-P10			2 3/4(69.8)	0.135(3.4)	0.056(1.4)	0.044(1.1)	0.089(2.3)	0.187(4.7)	0.173(4.4)	0.174(4.4)	540	12453			
MS-20001-P8			2 (50.8)	0.200(5.1)	0.076(1.9)	0.064(1.6)	0.179(4.5)	0.318(8.0)	0.302(7.7)	0.297(7.5)	860	12451			
MS-20001-P16			3 15/16(100)	0.287(7.3)	0.210(5.3)	0.196(5.0)	0.179(4.5)	0.509(12.9)	0.491(12.5)	0.750(19.0)	3,270	12456			

単位はインチ・()内寸法はmmを示します[四捨五入]。 Unit: inches/dimensions in parentheses: mm

●: RoHS指令対応品 ▲: RoHS指令に対応可能です。

※大量のご注文は更にお安くなります。