






SCHEMATIC



Rating	30VDC 0.3A / 16VDC 0.5A
Withstand Voltage	AC250V 1 minute
Insulation Resistance	≥ 100MΩ DC250V
Contact Resistance	≤ 50mΩ
Soldering Temper.	245±5°C 5 Sec.
Mechanical Life	100,000 cycles
Electrical Life	10,000 cycles
Operating Temper	-15°C - + 55°C
Shipping Temper	-25°C - + 65°C
Position Travel	1.5 ± 0.2 mm
Ambient Humidity Range	< 85%RH
Operating Force	200±80gf

NOTE: TOLERANCES UNLESS OTHERWISE SPECIFIED: ±0.2(mm).

RoHS Compliant

CW INDUSTRIES
Southampton, Pa. 18966
Tel 215.355.7080/www.cwind.com

Date Drawn: 3-21-12

Rev. 0

Unit: mm

Checked By: *G. Gold*

Title:

PUSH SWITCH

CW P/N:

GPBS850N