


**MIL-C-26482**
**MIL-C-83723**  
**Series I Bayonet**
**650DS001 B 16**

Basic Part No. \_\_\_\_\_

Finish (Table IV) \_\_\_\_\_

Shell Size \_\_\_\_\_


**TABLE III: DIMENSIONS**

| Shell Size | E Dia        | F Max        | G            | H Dia<br>±.010 (0.3) | J           | K          |
|------------|--------------|--------------|--------------|----------------------|-------------|------------|
| 08         | .471 (12.0)  | .828 (21.0)  | .594 (15.1)  | .120 (3.0)           | .478 (12.1) | .062 (1.6) |
| 10         | .588 (14.9)  | .954 (24.2)  | .719 (18.3)  | .120 (3.0)           | .478 (12.1) | .062 (1.6) |
| 12         | .748 (19.0)  | 1.047 (26.6) | .812 (20.6)  | .120 (3.0)           | .478 (12.1) | .062 (1.6) |
| 14         | .873 (22.2)  | 1.141 (29.0) | .906 (23.0)  | .120 (3.0)           | .478 (12.1) | .062 (1.6) |
| 16         | .998 (25.3)  | 1.234 (31.3) | .969 (24.6)  | .120 (3.0)           | .478 (12.1) | .062 (1.6) |
| 18         | 1.123 (28.5) | 1.328 (33.7) | 1.062 (27.0) | .120 (3.0)           | .478 (12.1) | .062 (1.6) |
| 20         | 1.248 (31.7) | 1.453 (36.9) | 1.156 (29.4) | .120 (3.0)           | .572 (14.5) | .094 (2.4) |
| 22         | 1.373 (34.9) | 1.578 (40.1) | 1.250 (31.8) | .120 (3.0)           | .572 (14.5) | .094 (2.4) |
| 24         | 1.498 (38.0) | 1.703 (43.3) | 1.375 (34.9) | .147 (3.7)           | .605 (15.4) | .094 (2.4) |

**TABLE IV: STANDARD FINISHES**

| Finish Symbol | Finish                    |
|---------------|---------------------------|
| B             | Cadmium Olive Drab        |
| C             | Anodize, Black            |
| M             | Electroless nickel        |
| NF            | 500 hr Cadmium Olive Drab |

1. For complete dimensions see Military Standard MS3115.
2. Metric dimensions (mm) are indicated in parentheses.