



FEATURES:

- Shielded cable to reduce noise
- WE-310 plugs molded to the cable to provide optimum durability

MATERIALS:

WE-310 Plug – Nickel plated brass

Cable – 4 Conductor shielded twisted pair, PVC jacket and insulation

RATINGS:

Operating Temperature: -20°C to +80°C

Operating Voltage: 300 VRMS Max.

Current: 1 Amperes @ 25°C Max.

ORDERING INFORMATION: Model 6318-96

Standard Length: 96 Inches (2134 mm)

All dimensions are in inches. Tolerances (except noted): .xx = ±.02" (.51 mm), .xxx = ± .005" (.127 mm).

All specifications are to the latest revisions. Specifications are subject to change without notice.

Registered trademarks are the property of their respective companies. Made in USA