




Field Interface Modules



Passive - 2 wire
32 Channel
Input
Allen-Bradley



Passive - 2 wire
32 Channel
Input
Allen-Bradley, GE Fanuc



Technical Data

Type	RS PLC DI 32PT			RS PLC 32PT 2x16		
Part number	998280	120 VAC, 10-30 VDC	1771-1AN, 1BN	998100	24 VDC	AB 1746-1B32
	998290	10-30 VDC	1771-1VN	998110	120/12/24/48 VAC	GEF IC697MDL250, 252, 253, 254
				998120	24 VDC	GEF IC697MDL650
				998121	12/24/48 VDC	GEF IC697MDL652, 653, 654
Rated voltage	See Above			See Above		
Rated current	2.0 A per channel / 12.0 A per module			3.0 A per channel / 3.0 A per group of 4 / 12.0 A per module		
Cable connection	(1) 1 x 40 pin IDC			(1) 1 x 40 pin IDC		
LED Indicators	No			No		
Operating Temperature	0°C...+50°C			0°C...+50°C		
Storage Temperature	-20°C...+60°C			-20°C...+60°C		
Dimensions LxWxH mm	194 x 70 x 55			194 x 70 x 55		
Terminal Wire Size	#26...14 AWG			#26...14 AWG		
Terminal Type	Screw Clamp			Screw Clamp		
Approvals						

Wiring Schematics

