



THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION ,19 .
© COPYRIGHT 19 BY AMP INCORPORATED. ALL INTERNATIONAL RIGHTS RESERVED.

LOC	DIST	P	F	REVISIONS			DATE	APPD
				ZONE	LTR	DESCRIPTION		
G	86				D	REV PER 063A-0561-01	07OCT02	JR/MS



- 1 TIN PL 0.00381 [0.000150] MIN THK PER MIL-T-10727
- 2 CIRCULAR MIL RANGE: 450-550 MCM



METRIC

276887-1					
PART NO					
DO NOT SCALE PRINT. UNLESS SPECIFIED DIMENSIONS IN mm [INCHES] TOLERANCES ON : 2 PLC DEC ± 0.51 [0.020] 3 PLC DEC ± - ANGLES ± - MATERIAL ANNEALED COPPER ASTM B-75 FINISH 1			DR 10/15/91 DK SCHRUM CHK 10/16/91 AJ KAUFMAN APPD 10/16/91 WJ VOCKROTH APPD 10/16/91 AJ ADELMANN PRODUCT SPEC - APPLICATION SPEC - WEIGHT -		
AMP AMP INCORPORATED Harrisburg, Pa. 17105			NAME TERMINAL, AMPPOWER™ WIRE SIZE: 253.0mm ² [500] MCM		
SIZE C		CAGE CODE 00779		DRAWING NO 276887	
SCALE 1:1		SHEET 1 OF 1			