

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

20

© COPYRIGHT 20


BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

LOC

DIST


REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	B	REVISED PER 0G3B-0119-01	03JAN2002	EZ	DB



CLOGGED CAVITY

CLAMPING SCREW



284045-2 AS SHOWN



MATERIALS AND FINISH
HOUSING: PA 6-6, UL 94-V0, COLOR GREEN.
CLAMP: BRASS, NICKEL PLATED.
DOUBLE SIDE CONTACT SPRING : PHOSPHOR BRONZE, TIN PLATED.
CLAMPING SCREW: M3, BRASS, NICKEL PLATED.

2



WIRE SIZE RANGE:
12 - 30 AWG.



NOT CUMULATIVE TOLERANCE.




SELECTIVE GOLD PLATING, 0.00076 [0.00030]



RETENTION LATCH

6.25 REF

12.5



MATING FACE

POLARIZATION KEY SLOT

2.54 REF

2.54 REF

10.16±0.10

GOLD PLATED ⁴	15.24	2	1-284045-4
	127.00	13	1-284045-3
	116.84	12	1-284045-2
	106.68	11	1-284045-1
	96.52	10	1-284045-0
	86.36	9	284045-9
	76.20	8	284045-8
	66.04	7	284045-7
	55.88	6	284045-6
	45.72	5	284045-5
TIN PLATED	35.56	4	284045-4
	25.40	3	284045-3
	15.24	2	284045-2
CONTACT FINISH	DIM.A	N° POS.	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT FOR TYCO ELECTRONICS CORPORATION
IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION
SHOULD BE CONTACTED FOR THE LATEST REVISION.

DIMENSIONS:	TOLERANCES UNLESS OTHERWISE SPECIFIED:
mm	
	0 PLC ±-
	1 PLC ±.3
	2 PLC ±.25
	3 PLC ±-
	4 PLC ±-
	ANGLES ±2
MATERIAL	FINISH
-	-

DWN	03JAN2002
CHK	E. ZANOLINI
APVD	03JAN2002
APVD	E. ZANOLINI
APVD	D. BIEVENOUR
PRODUCT SPEC	-
APPLICATION SPEC	-
WEIGHT	-
CUSTOMER DRAWING	

BUCHANAN

Tyco Electronics
Harrisburg, PA 17105-3608

NAME			
TERMINAL BLOCK VERTICAL PLUG STACKING LEFT HAND 10.16mm PITCH			
SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A3	00779	C=284045	-
SCALE	3:1	SHEET	OF 1
REV	B		