

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

130048-0193

Status:

Active

Overview:

industrial_ethernet_solutions

Description:

Micro-Change® (M12) Double-Ended Cordset, 4 Poles, Male (Straight) to Female (Straight) Crossover, 24 PVC, Cable 0.20m (7.87") Length

Documents:

Drawing (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification

UL

E200650

General

Product Family

Industrial Cordsets

Series

130048

Comments

Crossover

Connector End A

Micro-Change® (M12)

Connector End B

Micro-Change® (M12)

IP Rating

IP67

Overview

industrial_ethernet_solutions

Performance Category

5e

Product Name

Micro-Change® (M12)

Protocol

Ethernet

Region

America, Asia, Europe

Type

Double Ended

UPC

78678803951

Physical

Cable Diameter

5.59mm (.220")

Cable Length

0.20m (7.87")

Color - Cable Jacket

Teal

Coupling Style

Threaded

Gender

Male-Female

Keyway

D-coded

LED Indicator

No

Material - Cable Jacket

PVC

Material - Connector Body

PVC

Material - Contact

Copper Alloy

Material - Coupling Nut

Nickel-plated Brass

Material - Plating Mating

Gold over Nickel

Net Weight

35.590/g

Orientation

Straight

Poles

4

Temperature Range - Operating

-20°C to +75°C

Wire Size AWG

24

Wire/Cable Type

N/A

Electrical

Current - Maximum per Contact

1.5A

Voltage - Maximum

30V

Material Info


Old Part Number

E11B03003M002

Reference - Drawing Numbers

Sales Drawing

SD-120108-027



EU RoHS

RoHS Compliant by Exemption

REACH SVHC

Not Reviewed

Low-Halogen Status

Not Reviewed

China RoHS

50

Pb

Need more information on product environmental compliance?

Email productcompliance@molex.com

For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

130048Series

This document was generated on 10/02/2014

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION