

RAFIX 22 FS keylock switch, round collar

1.30.255.222/0000

Other lock variants available on request.



Included: 2 keys.

General information

Form of collar	round
Colout of front ring	metallized

Dimensions

Overall height	44.1 mm
Width of collar	---
Diameter of collar	29.8 mm
Length of collar	---
Mounting depth	9.2 mm
Mounting hole	22.3 mm
Key grid	30 x 30 mm

Mechanical characteristics

Torque max.	1.3 Nm
-------------	--------

Mechanical design


Key removal position	0+1
Number of locking positions	500
Mounting	ring nut
Illuminability	no
Rotating angle	1 x 90°, form L
Main key	no
Contact function	latching
Lock type	001
Lock	Micromec
Symmetric key	no
Wafers	5

Other specifications


Ambient temp. operating max.	+70 °C
Ambient temp. operating min.	-25 °C
ESD-strength lock / contact	15 kV
ESD-strength key/ front panel	15 kV
Resistance to constant environment	IEC 600 68-2-3 and 2-30
Storage temperature max.	+80 °C
Storage temperature min.	-40 °C
Operating life	0.3 million momentary / 50000 latching
Salt spray	IEC 600 68-2-11
Degree of protection from front side	IP65
Resistance at variable environment	IEC 600 68-2-14 and 2-33

16.07.2008

MASS



Else



Schaltw

