



main menu



- home
- test & measurement
- products
- skills
- download
- online catalogue T&M
- clamp-type test probes
- crocodile clips
 - ▶ 0,64 mm system
 - ▶ 2 mm system
 - ▶ 4 mm system
 - ▶ 4 mm safety system
- test probes
- oscilloscope test probes
- measuring leads
- plugs
- sockets
- sets
- miscellaneous
- company
- portrait
- corporate association
- location maps
- fairs and exhibitions
- jobs
- imprint
- terms and conditions

Home ▶ crocodile clips ▶ crocodile clips ▶ AK 2 B 2540 I


AK 2 B 2540 I

 datasheet for AK 2 B 2540 I
 article number: 972405101


View Full-Size Image



product description:	Bestellnummer: 972 405-101
description:	Contact-protected, high-strength, wide-opening alligator clip. Clamping range up to 30mm bolt diameter. Solid wire clip, U-shaped and fine wire section. Nickel-plated brass connecting socket, pluggable with 4mm safety measuring leads.
typ:	AK 2 B 2540 I rot/red
system:	4 mm safety system
order number:	972 405-101
clamping range:	30 mm
color versions:	
technical data	
type of contact:	clamp
type of termination:	4 mm socket (unsprung)
rated voltage:	AC/DC 1000 V
rated current:	32 A
contact resistance:	10 mOhm
material	
contact material:	brass
contact surface material:	nickel
housing material:	PP
environmental conditions:	
temperature range:	-30 °C to +90 °C
flammable class:	
housing:	UL 94 HB
drawing	



search online catalogue

Search

Search

Messetermine

No events

QR-Code

