





# REVISIONS

DOC. NO. SPC-F005 \* Effective: 7/8/02 \* DCP No: 1398

| DCP # | REV | DESCRIPTION          | DRAWN | DATE     | CHECKD | DATE    | APPRVD | DATE    |
|-------|-----|----------------------|-------|----------|--------|---------|--------|---------|
| 1876  | A   | RELEASED             | EO    | 07/25/06 | JN     | 2/13/08 | JN     | 2/13/08 |
| 1959  | B   | Shell Plate was Zinc | JN    | 2/13/08  | JN     | 2/13/08 | JN     | 2/13/08 |



RoHS  
Compliant



## PANEL CUTOUT

### SPECIFICATIONS:

1. Shell: Steel, Tin-Plate
2. Insulator: Glass Filled-Nylon, Black
3. Current Rating: 5 Amps
4. Dielectric Strength: 1000 V for One Minute
5. Insulator Resistance: 1000 Megohms Min.  
at 500 VAC
6. Temperature: -50°C to +105°C

DISCLAIMER:  
ALL STATEMENTS AND TECHNICAL INFORMATION CONTAINED HEREIN ARE BASED UPON INFORMATION AND/OR TESTS WE BELIEVE TO BE ACCURATE AND RELIABLE. SINCE CONDITIONS OF USE ARE BEYOND OUR CONTROL, THE USER SHALL DETERMINE THE SUITABILITY OF THE PRODUCT FOR THE INTENDED USE AND ASSUME ALL RISK AND LIABILITY WHATSOEVER IN CONNECTION THEREWITH.

### TOLERANCES:

Unless Otherwise  
Specified

.X ±0.35 [0.014]  
.XX ±0.25 [0.010]

### DRAWN BY:

EKLAS ODISH

### CHECKED BY:

Jason Nash

### APPROVED BY:

Jason Nash

### DATE:

07/25/06

### DATE:

2/13/08

### DATE:

2/13/08

### DRAWING TITLE:

15 Pin Crimp Type D-Sub Plug

### SIZE

A

### DWG. NO.

SPC15350

### ELECTRONIC FILE

79K4940.DWG

### REV

B




### SCALE: NTS

U.O.M.: mm [INCHES]


SHEET: 1 OF 2

**SPECIFICATIONS:**

1. Contact: Brass, Stamped 5u" Gold-Plated



**SECTION B-B**



**SECTION A-A**

ALL RIGHTS RESERVED. NO PORTION OF THIS PUBLICATION, WHETHER IN WHOLE OR IN PART CAN BE REPRODUCED WITHOUT THE EXPRESS WRITTEN CONSENT OF SPC TECHNOLOGY.

SPC-F005.DWG

DOC. NO. SPC-F005 \* Effective: 7/8/02 \* DCP No: 1388

SIZE  
**A**

DWG. NO.

**SPC15350**

ELECTRONIC FILE

**79K4940.DWG**

REV

**B**

SCALE: NTS

U.O.M.: mm [INCHES]

SHEET: 2 OF 2