






JKL LAMP NUMBER	VOLTS RATED	AMPS ±10%	MSCP ±25%	LUMENS ±25%	AVERAGE LIFE HRS.	FILAMENT TYPE
SM0640G	6.0	.040	.048	0.60	5,000	C-2V
SM06200G	6.0	.200	.334	4.20	5,000	C-2R
SM1220G	12.0	.020	.032	0.40	5,000	C-2V
SM1250G	12.0	.050	.160	2.01	5,000	C-2V
SM12100G	12.0	.100	.255	3.21	5,000	C-2V
SM2420G	24.0	.020	.064	0.80	5,000	C-2F
SM2450G	24.0	.050	.279	3.51	5,000	C-2F
SM3020G	30.0	.020	.104	1.31	5,000	C-2F
SM3050G	30.0	.050	.319	4.00	5,000	C-2F
SM4840G	48.0	.040	.358	4.50	5,000	CC-2F
SM6020G	60.0	.020	.184	2.30	5,000	CC-2F

METRIC  THIRD ANGLE PROJECTION		DIMENSIONS ARE IN MILLIMETERS TOLERANCE UNLESS OTHERWISE SPECIFIED 1 PL +/- 0.2 2 PL +/- 0		JKL COMPONENTS CORPORATION			
				TITLE T-2 TELEPHONE SLIDE BASE T6.8			
B DELETE PART NO. SM2845G A ADD SM3050G & SM6020G RELEASED	10/9/01 8/31/00 8/16/00	DRAWN BY L. WENGSTROM	APPVD BY DATE QC 10/9/01	SIZE A	FSCM NO. 55335	DRAWING NO. SLIDE BASE T6.8	
		- CAD DRAWING - MANUAL REVISIONS NOT PERMITTED		SCALE NONE		RELEASED DATE 8/16/00	REVISION DATE 10/9/01
REV. NO.	DESCRIPTION/ECO NUMBER	APPVD DATE			REV. NO. B	SHEET 1 OF 1	