


Receptacle

161-0507-E

KOBI CONN

Receptacle



Dimensions: mm.

SPECIFICATIONS	
Type:	PC mount, 8 pin DIN
Rating:	100VAC 2A, 24VDC 1A
Contact Resistance:	20mΩ max.
Insulation Resistance:	100MΩ min. @ 500VDC
Withstanding Voltage:	500VAC for 1 minute
Insertion Force:	4Kg max.
Withdrawal Force:	1~ 3.5Kg
Life:	5,000 cycles min.
Eath Terminal:	Tin plated phosphor bronze
Contact Terminal:	Tin plated brass
Terminal Insulation, body:	PBT
RoHS Compliant	

Date Last Revised: 8/7/12

Available from Mouser Electronics
1-800-346-6873 / www.mouser.com

KC-301192

Specifications are subject to change without notice. No liability or warranty implied by this information. Environmental compliance based on producer documentation.

161-0507-E

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Kobiconn:](#)

[161-0507-E](#)