





THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH

CHARACTERISTICS	ELECTRICAL DATA
OPERATING FORCE - - - - 2 1/2 LB MAX	CONTACT ARRANGEMENT S P D T
RELEASE FORCE - - - - - 3/4 LB MIN	L23 20A 125, <u>250</u> OR 480 VAC 10A 125 VAC "L"
DIFFERENTIAL TRAVEL - - - - .010 MAX	1HP 125 VAC, 2HP <u>250</u> VAC
OVERTRAVEL - - - - - .156 MIN	1/2A 125 VDC, 1/4A 250 VDC
SWITCH-BASIC RELACEMENT - - BA-2R70B-P7	 

THIRD ANGLE PROJECTION



SCALEFULL

DO NOT SCALE PRINT

UNLESS OTHERWISE SPECIFIED
TOLERANCES ARE

ONE PLACE	(.01)	$\pm .030$
TWO PLACE	(.00)	$\pm .015$
THREE PLACE	(.000)	$\pm .005$
ANGLES		$\pm$

WEIGHT .550 LB

NOTES

1 - ROLLER PLUNGER ASSEMBLY MAY BE SET AT ANY POSITION AROUND
AXIS OF PLUNGER

2 - 8-32 UNC X (.219) BINDER HEAD,COMBINATION ,TERMINAL SCREWS
AND CUPWASHERS