

RJ-11 and RJ-45 Modular Cable



- RJ-11 and RJ-45 modular cables are all-purpose cables for voice and data applications running at up to 1 Mbps

Conductor Gauge	28AWG	Connectors	6-wire; and 8-wire
Mutual Capacitance	72.2pF/m	Maximum Distance	As per equipment specifications
Outside Diameter	0.89mm	Pinning	Straight through
Resistance	15 ohms/100m		

Note: Not recommended for Token Ring or Ethernet applications

221516

Order Code		Price Each
RJ-11 Modular Cables (6-wire)		
1.2-m	754-948	
2.1-m	754-950	
4.3-m	754-961	
7.6-m	754-973	
RJ-45 Modular Cables (8-wire)		
1.2-m	754-985	
2.1-m	754-997	
4.3-m	755-000	
7.6-m	755-011	