

Model 2694

Turns Counting Dial

7/8" Diameter

Analog


For 6 mm shaft



SPECIFICATIONS¹

Counting Capacity, Maximum Turns	10
Shaft Diameter	6 mm
Bushing Diameter	3/8"
Depth – Maximum from face of panel	0.900"
Shaft Extension – Maximum from face of panel	0.781"
Shaft Extension – Minimum from face of panel	0.620"
Bushing Extension – Maximum from face of panel	0.300"
Locking Mechanism	Positive Action
Weight, nominal	16 grams
Number of set screws	1
Numeral Height	0.050"
Knob Material	Black Plastic
Dial Finish	White Numerals on Black Matte
Housing Finish	Satin Chrome
Operating Temperature Range	-55°C to 71°C

OUTLINE DIMENSIONS (inch/mm)



¹ Specifications subject to change without notice.