



Part No.	Emitting Color + Material	λ D (nm)	Lens Type	Iv (mcd) @10mA *20mA		Viewing Angle	Dimension
				Min.	Typ.		
L1060ID	GaAsP/GaP	625	red diffused	8	15	70°	1.8mm Round
L1060ED	GaAsP/GaP	625	orange diffused	8	15	70°	
L1060GD	GaP	568	green diffused	5	10	70°	
L1060YD	GaAsP/GaP	588	yellow diffused	5	8	70°	
L1060SRD	GaAlAs	640	red diffused	*70	*200	70°	
L1060SRC	GaAlAs	640	water clear	*100	*300	30°	

L21ID	GaAsP/GaP	625	red diffused	1.8	4	60°	2mm Round
L21ED	GaAsP/GaP	625	orange diffused	1.8	4	60°	
L21GD	GaP	568	green diffused	1.2	3	60°	
L21YD	GaAsP/GaP	588	yellow diffused	1.2	3	60°	
L21SGD	GaP	568	green diffused	*5	*6	60°	

L7104ID	GaAsP/GaP	625	red diffused	8	25	40°	T-1 (3mm) Round
L7104IT	GaAsP/GaP	625	red transparent	20	60	34°	
L7104EC	GaAsP/GaP	625	water clear	20	60	34°	
L7104ED	GaAsP/GaP	625	orange diffused	8	20	40°	
L7104GD	GaP	568	green diffused	8	20	40°	
L7104GT	GaP	568	green transparent	20	60	34°	
L7104GC	GaP	568	water clear	20	60	34°	
L7104YD	GaAsP/GaP	588	yellow diffused	5	15	40°	
L7104YT	GaAsP/GaP	588	yellow transparent	8	20	34°	
L7104YC	GaAsP/GaP	588	water clear	8	20	34°	
L7104ND	GaAsP/GaP	610	orange diffused	8	30	40°	
L7104NT	GaAsP/GaP	610	orange transparent	20	50	34°	
L7104NC	GaAsP/GaP	610	water clear	20	50	34°	
L7104PGD	GaP	555	green diffused	2	5	40°	
L7104PGT	GaP	555	green transparent	3	15	34°	
L7104PGC	GaP	555	water clear	3	15	34°	

L934HD	GaP	660	red diffused	1	3	60°	T-1 (3mm) Round
L934ID	GaAsP/GaP	625	red diffused	8	25	60°	
L934IT	GaAsP/GaP	625	red transparent	20	60	50°	
L934EC	GaAsP/GaP	625	water clear	20	60	50°	
L934ED	GaAsP/GaP	625	orange diffused	8	20	60°	
L934GD	GaP	568	green diffused	8	20	60°	
L934GT	GaP	568	green transparent	20	60	50°	
L934GC	GaP	568	water clear	20	60	50°	
L934YD	GaAsP/GaP	588	yellow diffused	5	15	60°	
L934YT	GaAsP/GaP	588	yellow transparent	8	20	50°	
L934YC	GaAsP/GaP	588	water clear	8	20	50°	
L934ND	GaAsP/GaP	610	orange diffused	8	30	60°	
L934NT	GaAsP/GaP	610	orange transparent	20	50	50°	
L934NC	GaAsP/GaP	610	water clear	20	50	50°	
L934PGD	GaP	555	green diffused	2	5	60°	
L934PGT	GaP	555	green transparent	3	15	50°	
L934PGC	GaP	555	water clear	3	15	50°	

NOTES :

- All dimensions are in millimeters (inches)
- Tolerance is $\pm 0.25\text{mm}$ ($0.01''$) unless otherwise noted.