

Jonard New Products

OK Industries Wire Wrap Tools

Pliers

Wrenches & Nut Drivers

Fiber Optic Products

CATV / Satellite Tools

Telecommunication Tools

Electrical Tools

Security & Alarm

Wire Strippers

Cable Installation (Fishing)

Punchdown Tools

Insulated Tools

Kynar Wire

Connector Tools

Solder and Desolder

IC Insertion and Extraction Tools

Force Gauges

Burnishers


Alignment Tools

Wire Wrapping Tools - Jonard

[New Products](#)

[Product Index](#)

[Download Product Catalog](#)



[VIEW LARGER IMAGE >>](#)



[KSW24 Wire Specification](#)



[KSW26 Wire Specification](#)



[KSW28 Wire Specification](#)



[KSW30 Wire Specification](#)

Kynar® KSW Insulated Silver Plated Copper Wire

For Cut/Strip/Wrap Applications. Low strip force Kynar® insulated wire is further processed to provide a low strip force for use with CSW bits and sleeves.

Ideally suited for many applications including production line work and wire wrapping. This wire is OFHC (oxygen free high conductivity) and provides a flexible yet abrasion resistant wire. The 24-28 AWG wire is UL 1422 (.005" insulation) and the 30 AWG wire is UL 1423 (.004" insulation). The wire is solid copper with 105° C maximum insulation temperature and all gauges are no voltage rated.

INCHES			METRIC				
Wire Size AWG	Insulation Diameter Inches	Roll Size Feet	BLUE	YELLOW	WHITE	BLACK	RED
24	.030	100	KSW 24B-0100	KSW 24Y-0100	KSW 24W-0100	KSW 24BLK-0100	KSW 24R-0100
26	.027	100	KSW 26B-0100	KSW 26Y-0100	KSW 26W-0100	KSW 26BLK-0100	KSW 26R-0100
28	.0235	100	KSW 28B-0100	KSW 28Y-0100	KSW 28W-0100	KSW 28BLK-0100	KSW 28R-0100
30	.0195	100	KSW 30B-0100	KSW 30Y-0100	KSW 30W-0100	KSW 30BLK-0100	KSW 30R-0100
		1000	KSW 30B-1000	KSW 30Y-1000	KSW 30W-1000	KSW 30BLK-1000	KSW 30R-1000