

**Part Number:** POM-3042P-R



#### Features

Omnidirectional  
Super clarity, distortion-free response  
Pin type mounting  
This part is RoHS 2002/95/EC Compliant


#### Electrical Specifications

|                   |                 |
|-------------------|-----------------|
| Directivity       | Omnidirectional |
| Impedance         | 2.2 kOhm        |
| Operating Voltage | 2 Vdc           |
| Package Size      | 6 x 3 mm        |
| Sensitivity       | -42 +/- 3 dB    |


Environmentally friendly

## Mechanical

*Dimensions are in millimeters, tolerance is  $\pm 0.5$  unless otherwise specified.*



## Performance



**For application notes and detail drawing specifications, please consult [www.projectsunlimited.com](http://www.projectsunlimited.com).**

Specifications subject to change without notice.

© 2006, Projects Unlimited Inc., All Rights Reserved.