



- Easy hand installation with low insertion force and economical assembly for a wide variety of applications
- Used where metal cushion clamps are typically used and eliminates the need for secondary fasteners.
- One-piece design significantly reduces installation time and provides the lowest installed cost.
- Prevents rotation of wire bundles and ensures secure grip on hoses with integrated ribs
- Designed to withstand years of use in a variety of environments.
- Offers strength over 125 lbs. (56.7kg) in shear, 70 lbs. (31.8kg) in tension.
- Integrated fastener requires a .275"-.288" (7.0mm-7.3mm) diameter hole and .125"-.140" (3.1mm-3.6mm) panel thickness
- Incorporates an impact modified Nylon 6.6
- Operates at a maximum temperature of 185°F (85°C) and a minimum temperature of -40°F (-40°C)

Part Number:	PC075-H25D-C0
Product Family:	<i>Pan-Clamp</i> ™ Heavy Duty Fixed Diameter Clamp
Product Line:	Push/Tree Barb
RoHS Compliancy Status:	Compliant
Part Description:	<i>Pan-Clamp</i> ™ Heavy Duty Fixed Diameter Clamp
Material:	Impact Modified Weather Resistant Nylon 6.6
Color:	Black
Width (In.):	.62

Width (mm):	15.7
Bundle Offset (mm):	21.1
Bundle Offset (In.):	.83
Environment:	Indoors/Outdoors
Max. Bundle Diameter (In.):	.75
Max. Bundle Diameter (mm):	19.1
Max. Panel Thickness (In.):	.126
Max. Panel Thickness (mm):	3.2
Mounting Method:	Push Barb
Panel Hole Diameter (In.):	.281
Panel Hole Diameter (mm):	7.1
Panel Thickness (In.):	.125 - .145
Panel Thickness (mm):	3.2 - 3.9
Std. Pkg. UOM:	PK
UOM:	PC
Std. Pkg. Qty.:	100
Min. Order Qty.:	100