

1



1

1

Notes:

- 1 Product and Processing must meet requirements of Tyco Electronics Standard 230-702
- 2 Includes dust caps (not shown on print).
- 3 IL tested at 1300nm.
- 4 Label 2 will not be present on any cable assembly less than 5 meters long.

DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED	
meters			
	0 PLC	±	-
	1 PLC	±	-
	2 PLC	±	-
	3 PLC	±	-
	6 PLC	±	-

Restricted To:

THIS INFORMATION IS CONFIDENTIAL AND PROPRIETARY TO TYCO ELECTRONICS CORPORATION AND ITS WORLDWIDE SUBSIDIARIES AND AFFILIATES. IT MAY NOT BE DISCLOSED TO ANYONE, OTHER THAN TYCO ELECTRONICS PERSONNEL, WITHOUT WRITTEN AUTHORIZATION FROM TYCO ELECTRONICS CORPORATION, HARRISBURG, PENNSYLVANIA

DAG NO

THIS DRAWING IS A CONTROLLED DOCUMENT.

LOC
CE
DIST
16

CAC Customer Layout Rev: D

Part #	L (meters)	L (feet)	LC-Duplex Secure, Aqua		SC-Duplex, Beige	
			IL (dB)	RL (dB)	IL (dB)	RL (dB)
0-1906078-1	0.950 - 1.050	3.11 - 3.44	0.5	-	0.5	-
0-1906078-2	1.950 - 2.050	6.39 - 6.72	0.5	-	0.5	-
0-1906078-3	2.950 - 3.050	9.67 - 10.00	0.5	-	0.5	-
0-1906078-4	3.920 - 4.080	12.86 - 13.38	0.51	-	0.51	-
0-1906078-5	4.920 - 5.080	16.14 - 16.66	0.51	-	0.51	-
0-1906078-6	5.920 - 6.080	19.42 - 19.94	0.51	-	0.51	-
0-1906078-7	6.920 - 7.080	22.70 - 23.22	0.51	-	0.51	-
0-1906078-8	7.920 - 8.080	25.98 - 26.50	0.51	-	0.51	-
0-1906078-9	8.850 - 9.150	29.03 - 30.01	0.51	-	0.51	-
1-1906078-0	9.850 - 10.150	32.31 - 33.30	0.52	-	0.52	-
1-1906078-1	10.850 - 11.150	35.59 - 36.58	0.52	-	0.52	-
1-1906078-2	11.850 - 12.150	38.87 - 39.86	0.52	-	0.52	-
1-1906078-3	12.850 - 13.150	42.15 - 43.14	0.52	-	0.52	-
1-1906078-4	13.850 - 14.150	45.43 - 46.42	0.52	-	0.52	-
1-1906078-5	14.850 - 15.150	48.72 - 49.70	0.52	-	0.52	-
1-1906078-6	15.840 - 16.160	51.96 - 53.01	0.52	-	0.52	-
1-1906078-7	16.830 - 17.170	55.21 - 56.33	0.53	-	0.53	-
1-1906078-8	17.820 - 18.180	58.46 - 59.64	0.53	-	0.53	-
1-1906078-9	18.810 - 19.190	61.71 - 62.95	0.53	-	0.53	-
2-1906078-0	19.800 - 20.200	64.96 - 66.27	0.53	-	0.53	-
2-1906078-1	20.790 - 21.210	68.20 - 69.58	0.53	-	0.53	-
2-1906078-2	21.780 - 22.220	71.45 - 72.90	0.53	-	0.53	-
2-1906078-3	22.770 - 23.230	74.70 - 76.21	0.53	-	0.53	-
2-1906078-4	23.760 - 24.240	77.95 - 79.52	0.54	-	0.54	-
2-1906078-5	24.750 - 25.250	81.20 - 82.84	0.54	-	0.54	-
2-1906078-6	25.740 - 26.260	84.44 - 86.15	0.54	-	0.54	-
2-1906078-7	26.730 - 27.270	87.69 - 89.46	0.54	-	0.54	-
2-1906078-8	27.720 - 28.280	90.94 - 92.78	0.54	-	0.54	-
2-1906078-9	28.710 - 29.290	94.19 - 96.09	0.54	-	0.54	-
3-1906078-0	29.700 - 30.300	97.44 - 99.40	0.55	-	0.55	-
3-1906078-1	30.690 - 31.310	100.68 - 102.72	0.55	-	0.55	-
3-1906078-2	31.680 - 32.320	103.93 - 106.03	0.55	-	0.55	-
3-1906078-3	32.670 - 33.330	107.18 - 109.35	0.55	-	0.55	-
3-1906078-4	33.660 - 34.340	110.43 - 112.66	0.55	-	0.55	-
3-1906078-5	34.650 - 35.350	113.68 - 115.97	0.55	-	0.55	-
3-1906078-6	35.640 - 36.360	116.92 - 119.29	0.55	-	0.55	-
3-1906078-7	36.630 - 37.370	120.17 - 122.60	0.56	-	0.56	-
3-1906078-8	37.620 - 38.380	123.42 - 125.91	0.56	-	0.56	-
3-1906078-9	38.610 - 39.390	126.67 - 129.23	0.56	-	0.56	-
4-1906078-0	39.600 - 40.400	129.92 - 132.54	0.56	-	0.56	-
4-1906078-1	40.590 - 41.410	133.16 - 135.85	0.56	-	0.56	-
4-1906078-2	41.580 - 42.420	136.41 - 139.17	0.56	-	0.56	-

Qty	U of M	Description	Item No.
2	piece	Trace Label	10
2	piece	CONN SUBASSY, MM, SC 1.6MM	9
4	piece	Eyelet/Shrink tube assembly - White	8
2	piece	SC Duplex Clip	7
AR	meter	2 Fiber, XG-50/125, 2.0mm, Twinzip, Aqua, OFNR (Riser)	6
2	piece	2.5mm ferrule cover	5
2	piece	SC Simplex Housing, Beige	4
2	piece	LC Connector Assy, 1.6mm-2.0mm, MM	3
1	piece	LC Duplex clip, black	2
4	piece	LC, SC, FC Straight Boot, Beige	1

	A	Rev Per EC#	RELEASE	4/21/2009	-
P	LTR	REVISION RECORD		DATE	DIN

DIMENSIONS; meters		TOLERANCES UNLESS OTHERWISE SPECIFIED	
	0 PLC	±	-
	1 PLC	±	-
	2 PLC	±	-
	3 PLC	±	-
	4 PLC	±	-

Restricted To:

Q1 Cable Assy Configurator		MATERIAL -		HEAT TREAT -	
CHK James Barry		 AMP Tyco Electronics, Inc. Harrisburg, PA 17105-3608			
APVD James Barry					
NAME FO C/A - 2 fiber, XG - 50/125, OFNR (Riser) jacket, LC-Duplex					
Section to SC-Duplex					
SCALE NTS		SIZE A2		DRAWING NO C- 1906078	
				SHEET 2 of 4	
				REV A	

D

C

B

A

THIS DRAWING IS A CONTROLLED DOCUMENT.

LOC
CE
DIST
16

CAC Customer Layout Rev: D

	A	Rev Per EC#	RELEASE	4/21/2009	-	JF			
P	LTR	REVISION RECORD	DATE	DIN	AP				

TOLERANCES UNLESS OTHERWISE SPECIFIED		
PLC	±	"
PLC	±	"
PLC	±	"
PLC	±	"
PLC	±	"

DIN Cable Assy Configurator		MATERIAL -		HEAT TREAT -	
CHK James Barry		 Tyco Electronics, Inc. Harrisburg, PA 17105-3608			
APVD James Barry					
NAME FO C/A - 2 fiber, XG - 50/125, OFNR (Riser) jacket, LC-Duplex					
Secure to SC-Duplex					
SCALE NTS		SIZE A2		DRAWING NO C- 1906078	
				SHEET 3 of 4	
				REV A	

	USED ON
--	---------

THIS INFORMATION IS CONFIDENTIAL AND PROPRIETARY TO TYCO ELECTRONICS CORPORATION. IT MAY NOT BE DISCLOSED TO ANY OTHERS WITHOUT THE WRITTEN AUTHORIZATION OF TYCO ELECTRONICS CORPORATION, HARRISBURG, PENNSYLVANIA.

THIS DRAWING IS A CONTROLLED DOCUMENT.

LOC
CE
DIST
16

CAC Customer Layout Rev: D

8 7 6 5 4 3 2 1

	A	Rev Per EC#	RELEASE	4/21/2009	-	JB	
P	LTR	REVISION RECORD		DATE	DIN	APVD	

DIMENSIONS: meters

TOLERANCES UNLESS OTHERWISE SPECIFIED:
0 P.L.C. ± .
1 P.L.C. ± .
2 P.L.C. ± .
3 P.L.C. ± .
4 P.L.C. ± .

Restricted To:

DIN Cable Assy Configurator		MATERIAL -	HEAT TREAT -	
CHK James Barry	AMP Tyco Electronics, Inc. Harrisburg, PA 17105-3608			
APVD James Barry				
NAME FO C/A - 2 fiber, XG - 50/125, OFNR (Riser) jacket, LC-Duplex Secure to SC-Duplex				
SCALE NTS	SIZE A2	DRAWING NO C- 1906078	SHEET 4 of 4	REV A

Label 1

Per specification 107-1645-1

Trace # - Bar Code

XXXXXXXXXXXXXXXXXX

Trace # - Human Readable

Logo

Made in XXXX

X-XXXXXXXX-X

Part Number

Country of Origin

This label is used on all lengths on this drawing.

Label 2

Per specification 107-1645-1

Trace # - Bar Code

XXXXXXXXXXXXXXXXXX

Trace # - Human Readable

Logo

Made in XXXX

X-XXXXXXXX-X

Part Number

Country of Origin

This label is used on all lengths on this drawing.

D
C
B
A