

NPN Silicon Epitaxial Planar Transistor**MMBT1616A****FEATURES**


- Audio frequency power amplifier.
- Medium speed switching.

**APPLICATIONS**

- General purpose application, switching application.

ORDERING INFORMATION

Type No.	Marking	Package Code
MMBT1616A	16A	SOT-23

**MAXIMUM RATING @ Ta=25°C unless otherwise specified**

Symbol	Parameter	Value	Units
V_{CBO}	Collector-Base Voltage	120	V
V_{CEO}	Collector-Emitter Voltage	60	V
V_{EBO}	Emitter-Base Voltage	6	V
I_C	Collector Current -Continuous	1000	mA
P_C	Collector Power Dissipation	350	mW
T_j, T_{stg}	Junction and Storage Temperature	-55~150	°C




NPN Silicon Epitaxial Planar Transistor**MMBT1616A****ELECTRICAL CHARACTERISTICS @ Ta=25°C unless otherwise specified**

Parameter	Symbol	Test conditions	MIN	TYP	MAX	UNIT
Collector-base breakdown voltage	$V_{(BR)CBO}$	$I_C=100\mu A, I_E=0$	120			V
Collector-emitter breakdown voltage	$V_{(BR)CEO}$	$I_C=1mA, I_B=0$	60			V
Emitter-base breakdown voltage	$V_{(BR)EBO}$	$I_E=100\mu A, I_C=0$	6			V
Collector cut-off current	I_{CBO}	$V_{CB}=60V, I_E=0$			0.1	μA
Emitter cut-off current	I_{EBO}	$V_{EB}=6V, I_C=0$			0.1	μA
DC current gain	h_{FE}	$V_{CE}=2V, I_C=100mA$ $V_{CE}=2V, I_C=1A$	135 81		400	
Collector-emitter saturation voltage	$V_{CE(sat)}$	$I_C=1A, I_B=50mA$			0.3	V
Base-emitter saturation voltage	$V_{BE(sat)}$	$I_C=1A, I_B=50mA$			1.2	V
Transition frequency	f_T	$V_{CE}=2V, I_C=100mA$	100			MHz
Collector output capacitance	C_{ob}	$V_{CB}=10V, I_E=0, f=1MHz$			19	pF
Turn on time	t_{on}	$V_{CE}=10V, I_C=100mA$		0.07		μS
Fall time	t_f	$V_{BE(off)}=2-3V$		0.07		μS
Storage time	t_s	$I_{B1}=I_{B2}=10mA$		0.95		μS

NPN Silicon Epitaxial Planar Transistor

MMBT1616A

TYPICAL CHARACTERISTICS @ $T_a=25^\circ\text{C}$ unless otherwise specified




NPN Silicon Epitaxial Planar Transistor

MMBT1616A


PACKAGE OUTLINE

Plastic surface mounted package

SOT-23



SOLDERING FOOTPRINT



PACKAGE INFORMATION

Device	Package	Shipping
MMBT1616A	SOT-23	3000/Tape&Reel