




YOUR SELECTED PRODUCT

For other versions than the listed available standard types, please contact PRECI-DIP



SPECIFICATIONS:

Socket contact with solder tail

- Press-in mount into dia 1.04 mm hole
- Materials: body brass, contact clip BeCu
- Electrical contact resistance max. 20 milliohms
- Mechanical life min. 500 cycles

AVAILABLE STANDARD TYPES

Ordering Part Number		Plating Body	Plating Clip	Insertion	Extraction	Dia.Gauge	Max Current
10005-83-2110	RoHS	5µm Sn	0.75µm Au	0.80 N	0.40 N	0.46 mm	3.0 A
10005-87-2110	RoHS	5µm Sn	Flash Au	0.80 N	0.40 N	0.46 mm	3.0 A