



English | 简体中文 | 日本語

Search by Part Number

GO

Search Site by keyword

GO

Contact IDT | Investors | Press

About IDT

Products

Applications

Support

myIDT

Calculators | Cross Reference | Green Initiative | Military | Parametric Search | Search by Part Number, Keyword, Document, Green/Pb-Free, Package

Home > Products > Display Solutions > Video Multiplexers/Switches > HDMI Multiplexer/Switches > VS421A > VS421APAG8

You may also like...

## VS421APAG8

|               |                           |
|---------------|---------------------------|
| Category:     | HDMI Multiplexer/Switches |
| Generic Part: | VS421A                    |
| Market Group: | VIDEO                     |
| Description:  | HDMI SWITCH               |

Time is money

### Parameters

|                         |          |
|-------------------------|----------|
| Speed                   | NA       |
| Temperature             | C        |
| Voltage                 | 5.0 V    |
| Status                  | Obsolete |
| Sample                  | Yes      |
| Minimum Order Quantity  | 2000     |
| Factory Order Increment | 2000     |

### Distributor Inventory

No Pricing information is available from our Distributors at this time.

### Documents

No documents available for this part at this time.

### Package

|                                  |                                |
|----------------------------------|--------------------------------|
| Package                          | TSSOP 48 (PAG48)               |
| Description                      | TSSOP 6.1 MM 0.5MM PITCH       |
| Status                           | Active                         |
| Class                            | PLASTIC                        |
| Category                         | Green                          |
| Pb (Lead) Free                   | Yes                            |
| Mark                             | PAG                            |
| Package Type                     | TSSOP                          |
| Lead Count                       | 48                             |
| Length                           | 12.5 mm                        |
| Width                            | 6.1 mm                         |
| Thickness                        | 1.0 mm                         |
| Pitch                            | 0.5 mm                         |
| Tube / Tray                      | TUBE                           |
| Quantity per Tube/Tray           | 38                             |
| Quantity per Reel                | 1000                           |
| Moisture Sensitivity Level (MSL) | 1                              |
| Moisture Exposure Floor Life     | Unlimited@<30C/85%RH           |
| Peak Reflow Temperature          | 260Â°C                         |
| Rebake Conditions                | NA                             |
| Related Package Documents        | <a href="#">view documents</a> |

[Home](#) | [Site Map](#) | [Legal](#) | [Careers](#) | [Contact Us](#) | [Quality](#) | [RSS](#) [What is this?](#)

Use of this website signifies your agreement to the [acceptable use](#) and [privacy policy](#). Copyright © 1997-2008 Integrated Device Technology, Inc. [All Rights Reserved](#).